



### Main

Commercial Status	Commercialised
Accessory / separate part category	Cabling accessories
Accessory / separate part type	Connector
Electrical connection	Elbowed female connector M12, 4 pins
Collar material	Metal
Status LED	Without
Cable connection	Screw terminal / wire size $\leq 0 \text{ in}^2$ (0.75 mm <sup>2</sup> ) / clamping capacity 0.12...0.24 in (3...6 mm)

### Complementary

Cable gland type	Pg 7
Cable connector fixing	Screw-on
[Ue] rated operational voltage	150 V DC 125 V AC
[In] rated current	3 A
Enclosure material	Plastic
Insulating resistance	> 1000 GΩ
Contact resistance	$\leq 8000 \mu\text{Ohm}$
Product weight	0.04 lb(US) (0.02 kg)

### Environment

IP degree of protection	IP67
Ambient air temperature for operation	-40...185 °F (-40...85 °C)

### Ordering and shipping details

Category	22483 - MACHINE CABLES
Discount Schedule	DS3
GTIN	00785901465966
Nbr. of units in pkg.	1
Package weight(Lbs)	0.06
Product availability	Non-Stock - Not normally stocked in distribution facility
Returnability	Y
Country of origin	HU

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0726 - <a href="#">Schneider Electric declaration of conformity</a>

### Contractual warranty

Period	18 months
--------	-----------