



“X” Dimension: 3276 = .23” (5,8mm), 4513 = .48” (12,2mm)

FEATURES:

- Threaded stud enables fast and easy mounting to panels.
- Solder turret allows wire attachment.
- Miniature banana plug spring features gold plated Beryllium Copper for long insertion life and low contact resistance.

Body: Brass, Gold Plated

Hex Nut: 4-40 Nut, Brass, Nickel Plated

RATINGS:

Operating Voltage: 2500 VDC

Current: 5 Amperes Max.

MATERIALS:

Miniature Banana Plug:

Spring – Beryllium Copper, Gold Plated

ORDERING INFORMATION: Model 3276 & 4513

Parts are packaged ten (10) per bag, unassembled.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ ” (.51 mm), .xxx = $\pm .005$ ” (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

4513