


Current Transformers - Indoor Toroidal (CT Series)



SMALL CURRENT TRANSFORMERS

- Toroidal design.
- Supplied with 24" insulated secondary leads, terminated with crimped ring connectors.
- Suitable for use with bare (uninsulated) primary conductor in circuits up to 600 V (4 KV Hi pot); or at higher voltages when a suitably insulated conductor is used.
- All units have 5 A secondary for use with standard AC ammeters with 5 A movements.
- Two hole mounting bracket on all models.

Part No.	Current Ratio Pri./Sec.	Accuracy %	Burden VA	Dimensions (Inches)						Mtg. Slots		Ship Wt. Lb.
				A	B	C	D	E	F	G	H	
CT50A	50:5	3.2	2	3.75	1.75	3.25	3.00	0.87	2.87	.22	.37	1.3
CT60A	60:5	2.4	2	3.75	1.75	3.25	3.00	0.87	2.87	.22	.37	1.4
CT75A	75:5	2.0	2	3.75	1.75	3.25	3.00	0.87	2.87	.22	.37	1.5
CT100A	100:5	2.0	2	3.75	1.75	3.25	3.00	1.20	2.87	.22	.37	1.1
CT150A	150:5	1.2	2	3.75	1.75	3.25	3.00	1.20	2.87	.22	.37	1.4
CT200A	200:5	1.2	2	4.75	1.75	4.25	4.00	2.20	3.87	.22	.37	1.7
CT250A	250:5	0.6	2	4.75	1.75	4.25	4.00	2.20	3.87	.22	.37	1.7
		1.2	5									
CT300A	300:5	0.6	2	4.75	1.75	4.25	4.00	2.20	3.87	.22	.37	1.8
		1.2	10									
CT400A	400:5	0.6	2	4.75	1.75	4.25	4.00	2.20	3.87	.22	.37	1.8
		1.2	10									
CT500A	500:5	0.3	2	4.75	1.75	4.25	4.00	2.20	3.87	.22	.37	1.8
		1.2	20									
CT600A	600:5	0.3	2	6.00	1.75	5.25	5.25	3.50	5.12	.28	.37	2.5
		1.2	20									
CT800A	800:5	0.3	5	6.00	1.75	5.25	5.25	3.50	5.12	.28	.37	2.8
		1.2	50									
CT1000A	1000:5	0.3	5	7.00	1.75	6.25	6.25	4.50	6.12	.28	.37	3.3
		1.2	50									
CT1200A	1200:5	0.3	10	8.00	1.75	7.25	7.25	5.50	7.12	.28	.37	3.8
		1.2	50									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[CT1000A](#) [CT200A](#) [CT75A](#) [CT50A](#) [CT600A](#) [CT60A](#) [CT150A](#) [CT1200A](#) [CT300A](#) [CT400A](#) [CT250A](#) [CT100A](#)
[CT500A](#) [CT800A](#)