

PRODUCT NO.	MATERIAL
68106-XXXLF	XYRON 340Z, COLOR BLACK, UL94V-0
68106-XXXHLF	ZYTEL FR50, COLOR BLACK, UL94V-0

EXTENDED RANGE

- TOOLING FEASIBILITY CONFIRMED
- SAMPLES ON DEMAND
- AVAILABILITY ON DEMAND

P/N	NO. of POS	A	B	C	D
68106-003LF	8	5.08	10.27	12.27	13.84
68106-003HLF					
68106-002LF	6	2.54	7.73	9.73	11.3
68106-002HLF					
68106-001LF	4	0	5.19	7.19	8.76
68106-001HLF					







FIG.1

PUT CAV.NO.1.2.3.4 IN THIS SURFACE



SECTION "X"-"X"

NOTES:

- 1 - PUT DD MARK IN THIS PLACE WITH 0.02/.008 HEIGHT.
- 2 - PUT CAV NO. 1.2.3.4. IN THIS PLACE WITH 0.02/.008 HEIGHT.
- 3 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 4 - THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.
- 5 - THIS PART SERIES IS NOT INITIALLY INTENDED FOR AUTOMOTIVE APPLICATIONS. ADDITIONAL FEES ARE CHARGEABLE FOR ANY ADDITIONAL QUALIFICATION AND TEST REPORTS PERFORMED OUTSIDE THE SCOPE OF THE STANDARD PRODUCT SPECIFICATIONS.
- 6 - UNLESS OTHERWISE APPROVED BY AMPHENOL, ALL PARTS AND COMPONENTS ARE DESIGNED & BUILT ACCORDING TO AMPHENOL'S SPECIFICATIONS WHICH ARE SUBJECT TO CHANGE WITHOUT NOTICE.

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family PV HOUSING
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
H	F-54565	DDE	25.02.10	angles	linear	mm	POLARIZED M/L HOUSING SHROUD DR
C	J8461	NY	87.05.08		.X ±0.3 .XX ±0.13 .XXX ±0.05	scale 1:1	
D	J03-044	YK	03.10.29	dr	D.DETOUILLOIN	18.06.27	dwg no
E	J05-0575	R.S	05.07.09	engr	L.MULIN	18.06.27	sheet 1 of 1
F	J06-0370	R.S	06.02.10	chr	L.MULIN	18.06.27	size
G	F-30562	DDE	18.06.27	appd	A.SOUDY	18.06.27	68106
sheet	revision						type
index	sheet						CUSTOMER Drawing

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[68106-002HLF](#) [68106-001LF](#) [68106-002LF](#) [68106-003LF](#)