

Heyco®-Tite Liquid Tight Cordgrips

Straight-Thru, PG* Hubs with Integral Sealing Ring

The Ultimate in Liquid Tight Strain Relief Protection

- Integral Sealing Ring ensures a superior seal at the clearance or threaded mounting hole location, every time.
- Widest range of approved cable diameters. Cable ranges listed are for the maximum IP68 sealing range. Contact Heyco for UL approved 514B cable ranges.
- IP 68 rated.
- Approved for **NEMA 4, 4X, 6 and 6P** applications.
- Ratchet design of sealing nut assembly provides superior anti-vibration protection and ensures a firm grip on the cable.
- Acme threads on body prevent skipping and speed installation.
- All nylon construction with Buna N or TPE sealing gland resists salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL.)
- Multiple sizes for flexible cord diameters ranging from .065" (1,7 mm) to 1.730" (44,0 mm).
- We recommend using the fitting with the smallest maximum diameter that will fit your application.
- **Unassembled Nylon Locknuts INCLUDED.**
- For Heyco Liquid Tight Threaded Plugs, see page 3-51.
- Consult Heyco for cordgrips molded in other colors.


CABLE DIA. RANGE				PART NO.			DESCRIPTION		PART DIMENSIONS							
Minimum	Maximum			Including Nylon Nut**		No Nut Black ††			A Clearance Hole Dia.	B Max. O.A. Length	C Thread Length	E Wrenching Nut Flats				
				Black	Gray											
in.	mm.	in.	mm.				in.	mm.	in.	mm.	in.	mm.				
Standard Thread																
.065	1,7	.210	5,3	M3444	M3445	M4754	RLTCG 7		.492	12,5	1.16	29,5	.32	8,1	.63	16,0
.115	2,9	.250	6,4	M3207	M3208	M4752	LTCG 7									
.065	1,7	.230	5,8	M3446	M3447	M4758	RLTCG 9		.599	15,2	1.25	31,8	.32	8,1	.82	20,8
.105	2,7	.315	8,0	M3210	M3211	M4756	LTCG 9									
.069	1,8	.260	6,6	M3448	M3449	M4762	RLTCG 11		.733	18,6	1.48	37,6	.38	9,7	.94	23,9
.230	5,8	.400	10,2	M3213	M3214	M4760	LTCG 11									
.095	2,4	.290	7,4	M4500	M4501	M4506	RLTCG 13.5		.804	20,4	1.53	38,9	.41	10,4	.98	24,9
.170	4,3	.450	11,4	M3216	M3217	M4764	LTCG 13.5									
.180	4,6	.400	10,2	M4502	M4503	M4508	RLTCG 16		.886	22,5	1.68	42,7	.44	11,2	1.06	26,9
.260	6,6	.545	13,8	M3219	M3220	M4766	LTCG 16									
.250	6,4	.490	12,4	M3454	M3455	M4748	RLTCG 21									
.420	10,7	.630	16,0	M3222GA	M3223GA	-	LTCG 21		1.12	28,3	1.89	48,0	.52	13,2	1.30	33,0
.435	11,0	.705	17,9	M3222	M3223	M4768										
.490	12,4	.785	19,9	M4504	M4505	M4512	RLTCG 29		1.470	37,3	2.23	56,6	.57	14,5	1.73	43,9
.590	15,0	1.000	25,4	M3225	M3226	M4770	LTCG 29									
.787	20,0	1.020	25,9	M3206	M3205	M4772	RLTCG 36		1.88	47,6	2.39	60,7	.47	11,9	2.05	52,7
.875	22,2	1.260	32,0	M3204	M3203	M4774	LTCG 36									
1.000	25,4	1.240	31,5	M3218	M3215	M4740	RLTCG 42		2.130	54,1	2.50	63,5	.48	12,2	2.46	62,5
1.230	31,2	1.560	39,6	M3212	M3209	M4742	LTCG 42									
1.160	29,5	1.350	34,3	M3283	M3284	M4744	RLTCG 48		2.340	59,4	2.63	66,7	.50	12,7	2.73	69,3
1.450	36,8	1.730	43,9	M3281	M3282	M4776	LTCG 48									
Short Thread																
.069	1,8	.260	6,6	M3448ST	M3449ST	-	RLTCG 11 ST		.733	18,6	1.41	35,8	.31	7,9	.94	23,9
.230	5,8	.400	10,2	-	-	M3213ST	LTCG 11 ST									
.250	6,4	.490	12,4	M3454ST	M3455ST	-	RLTCG 21 ST		1.115	28,3	1.80	45,7	.43	10,9	1.30	33,0
.435	11,0	.705	17,9	M3222ST	M3223ST	-	LTCG 21 ST									

Standard colors black and gray.


*Steel conduit threads per DIN 40430, see page 3-57

**Nylon locknuts shipped unassembled

††For No Nut Part Nos. in gray color please visit our Cordgrip product section at heyco.com



**SUGGESTED CLEARANCE HOLE
FOR NONTHEADED MOUNTING**



***Consult Heyco for Wrenching Nut Thickness "D"

*Quick
Specs*

Material
Certifications

Nylon 6/6 w/Buna N or TPE Sealing Gland

UL Listed under Underwriters' Laboratories File E51579

UL Recognized under the Component Program of Underwriters' Laboratories File E51579

SR Certified by Canadian Standard Association File 93876C

Approved for NEMA 4, 4X, 6 and 6P Applications

94V-2

Static -40°F (-40°C) to 239°F (115°C)

Dynamic -4°F (-20°C) to 212°F (100°C)

IP 68 (70 PSI, 5 BAR)

Flammability Rating
Temperature Range

IP Rating

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

[M3204](#) [M3446](#) [M3444](#) [M3448](#) [M3447](#) [M3449](#) [M3445](#) [M3211](#) [M3219](#) [M3213](#) [M3217](#) [M3216](#) [M3210](#) [M3214](#)
[M3207](#) [M3208](#) [M3220](#) [M3222](#) [M3226](#) [M3225](#) [M3223](#) [M3455](#) [M3454](#) [M4500](#) [M4504](#) [M4502](#) [M4505](#) [M4501](#)
[M4503](#) [M3209](#) [M3212](#) [M3215](#) [M3218](#) [M3281](#) [M3282](#) [M3283](#) [M3284](#) [M3222ST](#) [M3206](#) [M4768](#) [M3205](#) [M3203](#)
[M4509](#) [M3213ST](#) [M4754](#) [M4512](#) [M4753](#) [M4748](#) [M4759](#) [M4758](#) [M4774](#) [M4513](#) [M3455ST](#) [M4506](#) [M4763](#)
[M3454ST](#) [M4749](#) [M4769](#) [M4771](#) [M4772](#) [M4757](#) [M4766](#) [M4760](#) [M4765](#) [M4775](#) [M4755](#) [M4770](#) [M4762](#) [M4752](#)
[M4756](#) [M3223ST](#) [M4508](#) [M4767](#) [M4507](#) [M4761](#) [M4764](#) [M3214ST](#) [M3448ST](#) [M3449ST](#) [M4742](#) [M4745](#) [M4744](#)
[M4741](#) [M4743](#) [M4740](#) [M4760CB](#)