
a PennEngineering® Company



- Protects the lifeline of your electric/electronic products by absorbing the forces of pull, push, and twist that maybe exerted on the flexible power cord.
- Securely anchors, insulates, and protects cables at panel entry points.
- Sizes SR 2-Series to SR 6-Series for mounting hole diameters from .375" (9,5 mm) to .500" (12,7 mm).
- See page 4-38 for corresponding Mounting Hole Plugs which can be used to fill blank/unused Mounting Holes and thus allow for a single panel design for multiple applications.
- See pages 4-27 & 4-28 for SR assembly tools.
- See schematic on page 4-20.
- For Double D Mounting Hole Punches, see page 4-30.





Straight-Thru for Round Cables .375" (9,5 mm) to .500" (12,7 mm) Mounting Holes

WILL FIT THESE CABLES					PANEL DIMENSIONS					PART NO.	DESCRIPTION	PART	DIM.	Mounting
UL Type	AWG/ Conductors	Appro: Si		A Mounting Hole Dia.		B To Prevent Rotation		Finished Fit Panel Thickness*		Black		BO! LEN	DY	Hole Plug
		in.	mm.	in.	mm.	in.	mm.	in.	mm.			in.	mm.	PART NO.
AWM	12/1	.125- .187	3,2- 4,8	.375	9,5	.330	8,4	.062	1,6	1060	SR 2M-1	.406	10,3	2617
SV & SVT	18/2	.220- .245	5,6- 6,2	.500	12,7	.450	11,4	.062	1,6	1157	SR 5MN-3	.438	11,1	2491
Same as SR 5MN-3 above except						-	.100	2,5	1140	SR 5M-3	.438	11,1	2491	
For custor	m interlock	.250	6,4	.560	14,2	.730	18,5	.125	3,2	1487	SR 30-1A**	070		
cable, not UR		.265	6,7	.560	14,2	.730	18,5	.125	3,2	1490	SR 30-1B**	.672	17,1	consult Heyco
SV & SVT	18/2	.250	6,4	.500	12,7	.450					SR 5N-4	.438	11,1	2491
	18/3	.255	6,5	.500- .515	12,7- 13,1		11,4							
HPD	18/2	.270	6,9	.500	12,7			.062	1,6	1150				
	16/2	.290	7,4	.500- .515	12,7- 13,1									
SJT	18/2	.300	7,6	.531	13,5									
Same as SR 5N-4 above except								.100 .156	2,5 4,0	1147 1154	SR 5P-4 SR 5L-1	.438 .438	11,1 11,1	2491 consult Heyco
SV &	18/2	.255	6,5			.450	11,4			1137	SR 5P3-4	.438	11,1	2491
SVT	18/3	.270	6,9	.500	12,7			.100	2,5					
HPD	18/2	.290	7,4											
SJ, SJT & SJ0	18/2	.300 7,6	7,6	.500	12,7	.465	11,8	.090	2,3	1184	SR 6W-1	.438	11,1	2491
SPT-3	16/2													

Standard color black. Consult Heyco for white and other colors.



Material Certifications Nylon 6/6

Recognized under the Component Program of Underwriters' Laboratories File E15331

Certified by the Canadian Standards Association File 8919 94V-2 -.04°F (-18°C) to 221°F (105°C)

Flammability Rating Temperature Range

<sup>\*</sup>Maximum Panel Thickness. Part has additional clearance. Consult Heyco for your Custom Finished Fit Panel Thickness.

<sup>\*\*</sup>Use Elongated Mounting Hole.

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Heyco:

<u>1150</u> <u>1157</u> <u>1147</u> <u>1184</u> <u>1060</u> <u>1154</u> <u>1137</u> <u>1140</u> <u>1138</u> <u>1151</u> <u>1155</u> <u>1490</u> <u>1487</u> <u>1061</u> <u>1148</u> <u>1321</u> <u>1141</u> <u>1146</u> 1328 1184FJ 1485 1158 1185