



Dimensions: mm (in.)

| SPECIFICATIONS | |
|------------------------------|-------------------------------|
| Housing: | molded ABS plastic |
| Wire: | stripped & tinned (26 AWG) |
| Operating temperature range: | 32°F~176°F |
| Snaps: | nickel plated brass (6 prong) |
| Conductor: | copper (tin overcoated) |
| Ring terminals: | copper |
| Life cycle: | 400 insertions |
| RoHs Compliant | |

| Mouser Stock No. | Dim. A(in.) ±.118 |
|------------------|-------------------|
| 123-5114-GR | 3.94 |
| 123-5116-GR | 5.9 |
| 123-5118-GR | 7.87 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eagle Plastic Devices:](#)

[123-5116-GR](#) [123-5114-GR](#) [123-5118-GR](#)