
Last Update: 06-11-12 **Ref.** #: MS-100729

Dimensions: mm (in.)



POS.1	POS.2
7	-
ON	(ON)
2-3,5-6	2-1,5-4
2 Comm. 3	2 Comm. 0 3
5 Comm. 6	5 Comm. 6

Electrical Specifications:

- Electrical Life: 40,000 make-and-break cycles at full load
- Contact Resistance: $10m\Omega$ max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000M Ω min.
- Dielectric Strength: 1,000 V RMS@ sea level.
- Rating: 2A / 250 VAC

5A / 120 VAC or 28 VDC

Mechanical Specifications:

• Operating Temperature: -30° C to +85° C.

Materials:

- Case: Diallyl phthalate (DAP)
- Acutuator: Brass, chrome plated.
- Bushing: Brass, nickel plated.
- Housing: Stainless steel.
- Terminal/Contact: Silver or Gold plated.
- Switch Support: Brass, Tin plated.

Note:

RoHS compliant by exemption

Toggle Switch
108-1MD2T1B1M1QE-EVX



Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

108-1MD2T1B1M1QE-EVX