



Last Update: 6/18/12 **Ref.** #: MS-100887

Dimensions: mm (In.)











Without locking ring



With standard locking ring



P.C. Mounting

Mechanical Specifications:

- Mechanical Life: 30,000 make-and-break cycles
- Operating Temperature: -30°C to 85°C

Electrical Specifications:

- Rating: 1A / 250VAC, 3A / 120 VAC or 28 VDC
- Contact Resistance: 20mΩ max. initial @ 2-4VDC 100mA

Panel Mounting


- Insulation Resistance: 1,000M Ω min.
- Dieletric Strength: 1,000 V RMS@sea level

Materials:

- Case: Diallyl phthalate (DAP)
- Actuator: Brass, chrome plated
- Bushing: Brass, nickel plated
- Housing: Stainless Steel
- Switch Support: Brass, tin plated
- Terminals/Contact: Brass, with silver or gold plated

Note:

RoHS compliant by exemption



Sub-Miniature Toggle Switches

108-0043-EVX, 108-0046-EVX



www.mouser.com

1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

108-0043-EVX 108-0046-EVX