


Fuse Block > 354 Series

# 354 Series OMNI-BLOK® Molded Base Fuse Block for 3AB/3AG Fuses







#### **Agency Approval**

Agency	Agency File Number		
c <b>'RL</b> "us	E14721*		
<b>(</b>	7316**		

<sup>\* -</sup> UL Recognized to UL/CSA 4248.1 \*\* - CSA Certified to CSA C22.2 No 39-M1987

### **Product & Mounting Dimensions**





**Clip Detail** 

Solder 3/16' O.C. 3/16'







Note: Two different style clips can be supplied for circuit identity or polarization. Contact Littelfuse.

#### **Product Characteristics Compatible Fuses Size** 3AB/AG A low profile fuse block featuring individual barriers which reinforce the fuse clips while providing greater protection against clip damage and electrical shock. The unique design permits self-alignment of clips to fuse cap. This, plus a one-piece clip/ Description terminal assures low contact resistance. Higher currect ratings have been attained using spring brass clips. With the exception of the two-pole unit, multiple pole units may be broken apart to obtain desired number of poles **Dielectric Strength** 2200V., Minimum Tin plated phosphorus bronze except for Clip/Terminals 354900 series which is tin plated spring Glass reinforced Thermoplastic. UL 94V0 flammability rating. The standard base color is Gray except for 345 x21 items (single pole products which include anti-rotation Base boss option) where the standard base color is Black. Refer to the Ordering Information table on the following page for more information.

#### **Electrical Information**

**Ambient Temperature** 

Series or Catalog Number	Terminals	Rating
354 000	Solder	30A, 600 VDC/VAC*
354 600	3/16" Q.C.	20A, 600 VDC/VAC
354 700	1/4" Q.C032" Clip	30A, 600 VDC/VAC
354 800	1/4" Q.C.	20A, 600 VDC/VAC
354 900	1/4" Q.C.	30A, 600 VDC/VAC
354 101-GY	P.C. Board	15A, 600 VDC/VAC

-40°Cto +85°C

#### **Additional Information**







Samples

<sup>\*30</sup> amp capability is based on temperature rise with #10 AWG wire properly soldered.

# **Cartridge Fuse Blocks**

Fuse Block > 354 Series

### **Ordering Information**

Solder Terminals	NEMA Style 3/16" Quick Clip Terminals	1/4" Quick Clip Terminals	NEMA Style 1/4" Quick Clip .032" Terminals	NEMA Style 1/4" Quick Clip Terminals	Number of	Reference Dimension "A"
Ordering No.		Ordering No.		Poles	[mm]	
03540101ZXGY	-	-	-	-	1	.50" [12.7]
03540021ZXBL*	03540621ZXBL*	03540821ZXBL*	-	03540921ZXBL*	1	.50" [12.7]
03540001ZXGY	03540601ZXGY	03540801ZXGY	03540701ZXGY*	03540901ZXGY	1	.50" [12.7]
03540002ZXGY	03540602ZXGY	03540802ZXGY	03540702ZXGY	03540902ZXGY	2	1.12" [28.5]
03540003ZXGY	03540603ZXGY	03540803ZXGY	03540703ZXGY	03540903ZXGY	3	1.75" [44.5]
03540004ZXGY	03540604ZXGY	03540804ZXGY	03540704ZXGY	03540904ZXGY	4	2.38" [60.5]
03540005ZXGY	03540605ZXGY	03540805ZXGY	03540705ZXGY	03540905ZXGY	5	3.00" [76.2]
03540006ZXGY	03540606ZXGY	03540806ZXGY	03540706ZXGY	03540906ZXGY	6	3.63" [92.2]
03540007ZXGY	03540607ZXGY	03540807ZXGY	03540707ZXGY	03540907ZXGY	7	4.25" [108.0]
03540008ZXGY	03540608ZXGY	03540808ZXGY	03540708ZXGY	03540908ZXGY	8	4.88" [124.0]
03540009ZXGY	03540609ZXGY	03540809ZXGY	03540709ZXGY	03540909ZXGY	9	5.50" [139.7]
03540010ZXGY	03540610ZXGY	03540810ZXGY	03540710ZXGY	03540910ZXGY	10	6.13" [155.7]
03540011ZXGY	03540611ZXGY	03540811ZXGY	03540711ZXGY	03540911ZXGY	11	6.75" [171.5]
03540012ZXGY	03540612ZXGY	03540812ZXGY	03540712ZXGY	03540912ZXGY	12	7.38" [187.5]

<sup>\*</sup> With Anti-Rotation Boss

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

### Littelfuse:

```
03540012ZXGY
03540812ZXGY
03540909ZXGY
03540610ZXGY
03540009ZXGY
03540806ZXGY

03540807ZXGY
03540801ZXGY
03540901ZXGY
03540904ZXGY
03540902ZXGY
03540802ZXGY

03540609ZXGY
03540006ZXGY
03540612ZXGY
03540810ZXGY
03540906ZXGY
03540912ZXGY

03540601ZXGY
03540903ZXGY
03540907ZXGY
03540903ZXGY
03540602ZXGY
03540601ZXGY

03540908ZXGY
03540805ZXGY
03540608ZXGY
03540803ZXGY
03540621ZXBL
03540807ZXGY

03540605ZXGY
03540604ZXGY
03540803ZXGY
03540007ZXGY
03540010ZXGY

03540811ZXGY
03540910ZXGY
03540808ZXGY
03540008ZXGY
03540804ZXGY
03540011ZXGY

03540001ZXGY
03540603ZXGY
03540008ZXGY
03540804ZXGY
03540804ZXGY
03540011ZXGY
```