



**May not be suitable for all medical and aerospace applications.
Specifications: Contact Mallory Sonalert to discuss your application.**

NO CIRCUITRY

Oscillation Frequency (Hz)	2048
Operating Voltage (Vp-p)	1.25 ~ 2.5
Rated Voltage (Vp-p)	1.5
Current Consumption Max. (mA)	18 at Rated Voltage
Sound Pressure Level Min. (dB)	80 at 10cm at Rated Voltage
Coil Resistance (Ω)	42 ± 5
Operating Temperature ($^{\circ}\text{C}$)	$-20 \sim +70$
Storage Temperature ($^{\circ}\text{C}$)	$-30 \sim +80$
Housing	PPO plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Weight (Grams)	1.2
Options	For other options contact factory

Dimensions: (units: mm)**ROHS Compliant**

After Code Date 2017/06/13



Before Code Date 2017/06/12

Packaging: Parts are supplied in tube (40 per tube).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PB-0627PE-05AQ](#) [PB-1221PQ](#)