

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0002067103
Status: Active
Overview: Standard .062"+ and Standard .062" Pin and Socket Connector Systems
Description: 1.57mm Diameter, Standard .062" Pin and Socket PC Tail Terminal, Series 1779, Female, with 2.54µm Tin (Sn) Plated Brass Contact, Bag Packaged

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-1190-003-001 \(PDF\)](#)

General

Product Family Crimp Terminals
Series 1779
Application Power, Wire-to-Wire
Comments PC Tail Brass for Standard .062" Housing
Crimp Quality Equipment Yes
Overview Standard .062"+ and Standard .062" Pin and Socket Connector Systems
Product Name Standard .062"
UPC 800753618404

Physical

Gender Female
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.160/g
Packaging Type Bag
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 3.00mm max.
Wire Size AWG N/A
Wire Size mm² N/A

Material Info

Engineering Number 1779-(P909)L

Reference - Drawing Numbers

Packaging Specification PK-1190-003-001
Sales Drawing SD-1779-X-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant
REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

1779 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	11030002

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[02-06-7103](#)