

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0003092092](#)  
**Status:** **Active**  
**Overview:** [Standard .093" Pin and Socket Connectors](#)  
**Description:** 2.36mm Diameter Standard .093" Pin and Socket Plug Housings, 9 Circuits, 3 Rows

|                                                          |                                                               |
|----------------------------------------------------------|---------------------------------------------------------------|
| <b>Documents:</b>                                        |                                                               |
| <a href="#">Drawing (PDF)</a>                            | <a href="#">Product Specification PS-1292-001-001 (PDF)</a>   |
| <a href="#">3D Model</a>                                 | <a href="#">Product Specification PS-1292-002-001 (PDF)</a>   |
| <a href="#">3D Model (PDF)</a>                           | <a href="#">Packaging Specification PK-1292-001-001 (PDF)</a> |
| <a href="#">Product Specification PS-02-09-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>          |

|                                    |                                                                               |
|------------------------------------|-------------------------------------------------------------------------------|
| <b>Agency Certification</b>        |                                                                               |
| CSA                                | LR19980                                                                       |
| UL                                 | E29179                                                                        |
| <b>General</b>                     |                                                                               |
| Product Family                     | Crimp Housings                                                                |
| Series                             | <a href="#">1292</a>                                                          |
| Application                        | Power, Wire-to-Wire                                                           |
| Comments                           | 14.0A max. can be achieved when housing is used with 42477 or 42478 terminals |
| Overview                           | <a href="#">Standard .093" Pin and Socket Connectors</a>                      |
| Product Name                       | Standard .093"                                                                |
| UPC                                | 800753614888                                                                  |
| <b>Physical</b>                    |                                                                               |
| Circuits (maximum)                 | 9                                                                             |
| Color - Resin                      | Natural                                                                       |
| Flammability                       | 94V-2                                                                         |
| Gender                             | Plug                                                                          |
| Glow-Wire Capable                  | No                                                                            |
| Material - Resin                   | Nylon                                                                         |
| Net Weight                         | 3.542/g                                                                       |
| Number of Rows                     | 3                                                                             |
| Packaging Type                     | Bag                                                                           |
| Panel Mount                        | No                                                                            |
| Pitch - Mating Interface           | 5.03mm                                                                        |
| Pitch - Termination Interface      | 5.03mm                                                                        |
| Stackable                          | No                                                                            |
| Temperature Range - Operating      | -40° to +105°C                                                                |
| <b>Solder Process Data</b>         |                                                                               |
| Lead-freeProcess Capability        | N/A                                                                           |
| <b>Material Info</b>               |                                                                               |
| Engineering Number                 | 1292-P1                                                                       |
| <b>Reference - Drawing Numbers</b> |                                                                               |
| Packaging Specification            | PK-1292-001-001                                                               |
| Product Specification              | PS-02-09-001, PS-1292-001-001, PS-1292-002-001                                |
| Sales Drawing                      | SD-1292-0001-001                                                              |



Series image - Reference only

|                                                                                                                                                                                                                                                  |                                                                                               |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------|
| <b>EU ELV</b><br><b>Not Relevant</b>                                                                                                                                                                                                             |                                                                                               |
| <b>EU RoHS</b><br><b>Compliant</b><br><b>REACH SVHC</b><br>Not Contained Per -<br>D(2021)4569-DC (8<br>July 2021)<br><b>Halogen-Free</b><br><b>Status</b><br><b>Low-Halogen</b><br>For more information, please visit <a href="#">Contact US</a> | <b>China RoHS</b><br><br><br><br><br><br><br><br><br><br>China ROHS<br>ELV<br>RoHS Phthalates |
|                                                                                                                                                                                                                                                  | Green Image<br>Not Relevant<br>Not Contained                                                  |

**Search Parts in this Series**  
[1292](#) Series

**Mates With**  
[03091091](#) , [03091092](#) , [03091093](#) ,  
[03091094](#)

**Use With**  
[1189](#) Crimp Terminals, [1190](#) Crimp Terminals, [1380](#) Male Crimp Terminals, [1381](#) Female Crimp Terminals, [1433](#) Crimp Terminals, [1434](#) Male Crimp Terminals, [1973](#) , [2151](#) , [2273](#) , [2870](#) , [2871](#) , [4272](#) , Link:4550, [6271](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[03-09-2092](#)