

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190390004

Status:

Active

Overview:

Snap Plugs and Receptacles

Description:

Avikrimp Snap Plug Receptacle for 18-22 AWG Wire, PVC, Fits Male Plug Diameter 4.57mm

Documents:	
3D Model	Product Specification PS-19902-011-001 (PDF)
3D Model (PDF)	Product Specification PS-19902-013-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E152602

General

Product Family	Quick Disconnects
Series	19039
Comments	Fits Male Plug Dia. 4.57mm
Crimp Quality Equipment	Yes
Insulated	Fully
Overview	Snap Plugs and Receptacles
Product Name	Avikrimp
Type	Snap Receptacle
UPC	800753049352

Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-0
Gender	Female
Glow-Wire Capable	No
Insulation	PVC
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	1.367/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Tab Thickness	N/A
Tab Width	N/A
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.25mm max.
Wire Size AWG	18, 20, 22

Electrical


Voltage - Maximum	Per Wire Specification
-------------------	------------------------

Material Info

Engineering Number	BRA-8180
--------------------	----------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
-----------------------	------------------------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19039 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	640012300
Crimp Head for the AT-200 Pneumatic Hand Tool	640052300

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19039-0004](#)