

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192160009

Status:

Active

Description:

Ultimate Wire Tap, Yellow, 12 AWG

|                |                                              |
|----------------|----------------------------------------------|
| Documents:     |                                              |
| 3D Model       | Product Specification PS-19902-011-001 (PDF) |
| 3D Model (PDF) | Product Specification PS-19902-013-001 (PDF) |
| Drawing (PDF)  | RoHS Certificate of Compliance (PDF)         |

|                      |         |
|----------------------|---------|
| Agency Certification |         |
| CSA                  | LR18689 |
| UL                   | E79133  |

|                         |                           |
|-------------------------|---------------------------|
| General                 |                           |
| Product Family          | IDT and Solder Connectors |
| Series                  | 19216                     |
| Crimp Quality Equipment | Yes                       |
| Product Name            | Wire Tap                  |
| UPC                     | 800753056268              |

|                                |                 |
|--------------------------------|-----------------|
| Physical                       |                 |
| Circuits (Loaded)              | 1               |
| Circuits (maximum)             | 1               |
| Color - Resin                  | Natural         |
| Durability (mating cycles max) | 25              |
| Flammability                   | 94V-2           |
| Gender                         | N/A             |
| Glow-Wire Capable              | No              |
| Lock to Mating Part            | None            |
| Material - Metal               | Phosphor Bronze |
| Material - Plating Mating      | Tin             |
| Material - Resin               | Nylon           |
| Net Weight                     | 1.080/g         |
| Number of Rows                 | 0               |
| Packaging Type                 | Bag             |
| Panel Mount                    | No              |
| Pitch - Mating Interface       | N/A             |
| Pitch - Termination Interface  | N/A             |
| Polarized to Mating Part       | Yes             |
| Stackable                      | No              |
| Temperature Range - Operating  | 105°C           |
| Wire Insulation Diameter       | N/A             |
| Wire Size AWG                  | 12              |

|                   |      |
|-------------------|------|
| Electrical        |      |
| Voltage - Maximum | 600V |

|                             |     |
|-----------------------------|-----|
| Solder Process Data         |     |
| Lead-freeProcess Capability | N/A |

|                    |       |
|--------------------|-------|
| Material Info      |       |
| Engineering Number | WT-12 |

|                             |                                    |
|-----------------------------|------------------------------------|
| Reference - Drawing Numbers |                                    |
| Product Specification       | PS-19902-011-001, PS-19902-013-001 |
| Sales Drawing               | SD-19216-008-001                   |



Series image - Reference only

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2021)4569-DC (8 July 2021)              |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Low-Halogen                                                   |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

19216 Series

Mates With

Male Quick Disconnect

This document was generated on 09/23/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19216-0009](#)