

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0398800303

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

5.08mm Pitch, Beau Eurostyle Low Profile, Fixed Block, Modular, 3 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Terminal Blocks

Series

39880

Application

N/A

Component Type

One Piece

Overview

Eurostyle Terminal Blocks

Product Name

Eurostyle Fixed Mount

Type

Euro Block

UPC

800753319042

Physical

Circuits (Loaded)

3

Entry Angle

Horizontal

Flammability

94V-0

Lock to Mating Part

None

Net Weight

2.670/g

Number of Rows

1

Orientation

Vertical

PC Tail Length

3.50mm

PCB Retention

None

PCB Thickness - Recommended

2.40mm

Panel Mount

No

Pitch - Mating Interface

5.08mm

Pitch - Termination Interface

5.08mm

Polarized to Mating Part

N/A

Shrouded

Fully

Stackable

Yes

Temperature Range - Operating

105°C

Wire Size AWG

16, 18, 20, 22, 24, 26, 28, 30

Wire Size mm²

0.20-1.50

Electrical

Current - Maximum per Contact

13.5A

Voltage - Maximum

300V

Material Info

Engineering Number

MX-MSB03005-0N

Reference - Drawing Numbers

Sales Drawing

SD-39880-003-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

39880 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39880-0303](#)