


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0510041000
Status: Active
Overview: MicroBlade™ Connection System
Description: 2.00mm Pitch MicroBlade™ Wire-to-Board Housing, Friction Lock, 5.80mm Height, 10 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-51004-002-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	51004
Application	Signal, Wire-to-Board
Overview	MicroBlade™ Connection System
Product Name	MicroBlade™
UPC	800753575998
Physical	
Circuits (maximum)	10
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	267.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-20°C to +85°C
Electrical	
Current - Maximum per Contact	2.0A
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-51004-002-001
Sales Drawing	SD-51004-**00



Series image - Reference only

EU ELV
Not Relevant

EU RoHS
Compliant
REACH SVHC
Not Contained Per
-ED/01/2017 (12
January 2017)
Halogen-Free
Status
Not Low-Halogen
**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
51004 Series

Mates With
53014 , 53015 , 53025 MicroBlade™
Headers

Use With
50011 Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[51004-1000](#)