



DESCRIPTION: 970 SERIES D-SUB BACKSHELL

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) 4-40 THUMBSCREWS
- (2) HOUSING SCREWS/NUTS
- (1) SET OF COMPRESSION INSERTS - VARIOUS SIZES
Ø0.157 [4.0], Ø0.197 [5.0], Ø0.276 [7.0], Ø0.354 [9.0]

MATERIAL: ABS POLYLAC / BLACK UL 94-HB
JACKSCREWS: STEEL - BLACK OXIDE
M3 HOODSCREWS: STEEL - BLACK OXIDE
COMPRESSION INSERT: ABS UL 94-HB
M3 NUT: STEEL, BLACK OXIDE
OPERATING TEMP: -30°C TO +90°C

**NOTE: 3 in-lbs IS RECOMMENDED TORQUE FOR HOUSING SCREWS





DIMENSIONS (in/mm)				
No. OF PINS	A	B	C	D
9	1.228	0.984	1.571	0.590
	31.19	24.99	39.90	14.99
15	1.555	1.312	1.634	0.590
	39.50	33.32	41.50	14.99
25	2.102	1.852	1.913	0.590
	53.39	47.04	48.59	14.99
37	2.744	2.500	2.110	0.590
	69.70	63.50	53.59	14.99

970-YYY-010R011

SERIES
POSITIONS
009
015
025
037
MATERIAL
010 = PLASTIC
COLOR
01 = BLACK
PUT-UPS
1 = KIT

UNITS = INCHES [MM]



	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 6-09-05	
	SCALE NTS		SHEET 1 OF 2		REV 11
	DWG NO. 970 -YYY-010R011				

RoHS COMPLIANT

NorComp

DESCRIPTION: 970 SERIES D-SUB BACKSHELL

MATERIAL: STEEL
PLATING: ZINC, BLACK



PLASTIC INSERTS

UNITS = INCHES [MM]



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS

DATE:
6-09-05

NorComp

SCALE
NTS

SHEET
2 OF 2

REV
11

DWG NO. 970 -YYY-010R011

RoHS COMPLIANT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

[970-009-010R011](#) [970-037-010R011](#) [970-025-010R011](#) [970-015-010R011](#)