

A. System Overview

Pre-Printed Marker Cards PCM Type

- Marker cards printed in a variety of legends allows “kitting” for project builds

- Plastic liner provides easy removal of markers while protecting unused markers

B1. Cable Ties

B2. Cable Accessories

B3. Stainless Steel Ties

C1. Wiring Duct

C2. Surface Raceway

C3. Abrasion Protection

C4. Cable Management

D1. Terminals

D2. Power Connectors

D3. Grounding Connectors

E1. Labeling Systems


E2. Labels

E3. Pre-Printed & Write-On Markers


E4. Permanent Identification

E5. Lockout/Tagout & Safety Solutions

F. Index



PCM-7



PCM-1-6

Material Chart

Material	Print Method	Temperature Range	Features
Vinyl Cloth, White	Pre-Printed	-50°F to 170°F (-46°C to 77°C)	Indoor/outdoor rated; conformable material with repositionable adhesive allows label to be removed and reused or used in temporary applications; provides durability, high temperature resistance, and dimensional stability for rough or textured surfaces; resists oil and abrasion.

		Width		Length		Markers Per Card	Std. Pkg. Card(s)	Std. Ctn. Card(s)
Part Number	Legend	In.	mm	In.	mm			
PCM-0	0							
thru	thru	0.25	6.35	1.50	38.1	36	25	100
PCM-99	99							
PCM-100	100							
thru	thru	0.36	9.14	1.50	38.1	25	25	100
PCM-202	202							
PCMH-0	0							
thru	thru	0.25	6.35	1.50	38.1	72	25	100
PCMH-25	25							
PCM-1-3	1 thru 3	0.25	6.35	1.50	38.10	36	25	100
PCM-1-4	1 thru 4	0.25	6.35	1.50	38.10		25	100
PCM-1-5	1 thru 5	0.25	6.35	1.50	38.10		25	100
PCM-1-6	1 thru 6	0.25	6.35	1.50	38.10		25	100
PCM-1-8	1 thru 8	0.25	6.35	1.50	38.10		25	100
PCM-1-9	1 thru 9	0.25	6.35	1.50	38.10		25	100
PCM-0-9	0 thru 9	0.25	6.35	1.50	38.10		25	100
PCM-1-10	1 thru 10	0.25	6.35	1.50	38.10		25	100
PCM-1-12	1 thru 12	0.25	6.35	1.50	38.10		25	100
PCM-1-16	1 thru 16	0.25	6.35	1.50	38.10		25	100
PCM-1-18	1 thru 18	0.25	6.35	1.50	38.10		25	100
PCM-19-36	19 thru 36	0.25	6.35	1.50	38.10		33	25
PCM-1-33	1 thru 33	0.27	6.91	1.50	38.10	25		100
PCM-34-66	34 thru 66	0.27	6.91	1.50	38.10	25		100
PCM-67-99	67 thru 99	0.27	6.91	1.50	38.10	25		100
PCM-100-124	100 thru 124	0.36	9.14	1.50	38.10	25	25	100
PCM-125-149	125 thru 149	0.36	9.14	1.50	38.10		25	100
PCM-150-174	150 thru 174	0.36	9.14	1.50	38.10		25	100
PCM-175-199	175 thru 199	0.36	9.14	1.50	38.10		25	100
PCM-200-224	200 thru 224	0.36	9.14	1.50	38.10		25	100
PCM-225-249	225 thru 249	0.36	9.14	1.50	38.10		25	100
PCM-250-274	250 thru 274	0.36	9.14	1.50	38.10		25	100
PCM-275-299	275 thru 299	0.36	9.14	1.50	38.10		25	100
PCM-300-324	300 thru 324	0.36	9.14	1.50	38.10		25	100
PCM-325-349	325 thru 349	0.36	9.14	1.50	38.10		25	100
PCM-350-374	350 thru 374	0.36	9.14	1.50	38.10		25	100
PCM-375-399	375 thru 399	0.36	9.14	1.50	38.10		25	100
PCM-400-424	400 thru 424	0.36	9.14	1.50	38.10		25	100
PCM-425-449	425 thru 449	0.36	9.14	1.50	38.10		25	100
PCM-450-474	450 thru 474	0.36	9.14	1.50	38.10		25	100
PCM-475-499	475 thru 499	0.36	9.14	1.50	38.10		25	100
PCM-500-524	500 thru 524	0.36	9.14	1.50	38.10	25	100	

Pre-Printed Marker Cards PCM Type (continued)



PCM-A1

Part Number	Legend	Width		Length		Markers Per Card	Std. Pkg. Card(s)	Std. Ctn. Card(s)
		In.	mm	In.	mm			
PCM-A thru PCM-Z	A thru Z	0.25	6.35	1.50	38.1	36	25	100
PCM-A-Z	A thru Z	0.25	6.35	1.50	38.1		25	100
PCM-A-Z-0-9	A thru Z 0 thru 9	0.25	6.35	1.50	38.1		25	100
PCM-A1 thru PCM-A4	A1 thru A4	0.25	6.35	1.50	38.1		25	100
PCM-B1 thru PCM-B5	B1 thru B5	0.25	6.35	1.50	38.1		25	100
PCM-C1 thru PCM-C4	C1 thru C4	0.25	6.35	1.50	38.1		25	100
PCM-E1 thru PCM-E3	E1 thru E3	0.25	6.35	1.50	38.1		25	100
PCM-F1 thru PCM-F4	F1 thru F4	0.25	6.35	1.50	38.1		25	100
PCM-H1 thru PCM-H5	H1 thru H5	0.25	6.35	1.50	38.1		25	100
PCM-L1 thru PCM-L5	L1 thru L5	0.25	6.35	1.50	38.1		25	100
PCM-M1 thru PCM-M2	M1 thru M2	0.25	6.35	1.50	38.1		25	100
PCM-P1 thru PCM-P3	P1 thru P3	0.25	6.35	1.50	38.1		25	100
PCM-R1 thru PCM-R5	R1 thru R5	0.25	6.35	1.50	38.1		25	100
PCM-S1 thru PCM-S5	S1 thru S5	0.25	6.35	1.50	38.1		25	100
PCM-T1 thru PCM-T9	T1 thru T9	0.25	6.35	1.50	38.1		25	100
PCM-X1 thru PCM-X4	X1 thru X4	0.25	6.35	1.50	38.1		25	100

Table continues on page E3.6

A.
System
Overview

B1.
Cable Ties

B2.
Cable
Accessories

B3.
Stainless
Steel Ties

C1.
Wiring
Duct

C2.
Surface
Raceway

C3.
Abrasion
Protection

C4.
Cable
Management

D1.
Terminals

D2.
Power
Connectors

D3.
Grounding
Connectors

E1.
Labeling
Systems

E2.
Labels

E3.
Pre-Printed
& Write-On
Markers

E4.
Permanent
Identification

E5.
Lockout/
Tagout
& Safety
Solutions

F.
Index

A.
System
Overview

B1.
Cable Ties

B2.
Cable
Accessories

B3.
Stainless
Steel Ties

C1.
Wiring
Duct

C2.
Surface
Raceway

C3.
Abrasion
Protection

C4.
Cable
Management

D1.
Terminals

D2.
Power
Connectors

D3.
Grounding
Connectors

E1.
Labeling
Systems

E2.
Labels

E3.
Pre-Printed
& Write-On
Markers

E4.
Permanent
Identification

E5.
Lockout/
Tagout
& Safety
Solutions

F.
Index




Pre-Printed Marker Cards PCM Type (continued)



PCM-1T1

Part Number	Legend	Width		Length		Markers Per Card	Std. Pkg. Card(s)	Std. Ctn. Card(s)
		In.	mm	In.	mm			
PCM-1L1	1L1					25	25	100
thru	thru	0.36	9.14	1.50	38.10			
PCM-1L3	1L3						25	100
PCM-2L1	2L1							
thru	thru	0.36	9.14	1.50	38.10		25	100
PCM-2L3	2L3							
PCMH-3L1	3L1						25	100
thru	thru	0.36	9.14	1.50	38.10			
PCMH-3L3	3L3						25	100
PCM-4L1	4L1							
thru	thru	0.36	9.14	1.50	38.10		25	100
PCM-4L3	4L3							
PCM-1T1	1T1					25	25	100
thru	thru	0.36	9.14	1.50	38.10			
PCM-1T3	1T3						25	100
PCM-3T1	3T1							
thru	thru	0.36	9.14	1.50	38.10		25	100
PCM-3T3	3T3							



Part Number	Color	Width		Length		Markers Per Card	Std. Pkg. Card(s)	Std. Ctn. Card(s)
		In.	mm	In.	mm			
PCM-BLK	Black	.25	6.35	1.50	38.10	36	25	100
PCM-BRN	Brown	.25	6.35	1.50	38.10		25	100
PCM-DBL	Dark Blue	.25	6.35	1.50	38.10		25	100
PCM-DGN	Dark Green	.25	6.35	1.50	38.10		25	100
PCM-GRY	Gray	.25	6.35	1.50	38.10		25	100
PCM-LBL	Light Blue	.25	6.35	1.50	38.10		25	100
PCM-LGN	Light Green	.25	6.35	1.50	38.10		25	100
PCM-ORN	Orange	.25	6.35	1.50	38.10		25	100
PCM-PNK	Pink	.25	6.35	1.50	38.10		25	100
PCM-PUR	Purple	.25	6.35	1.50	38.10		25	100
PCM-RED	Red	.25	6.35	1.50	38.10		25	100
PCM-TAN	Tan	.25	6.35	1.50	38.10		25	100
PCM-WHT	White	.25	6.35	1.50	38.10		25	100
PCM-YEL	Yellow	.25	6.35	1.50	38.10		25	100

Marker size:

Full size marker – 1.50" (38.10mm). Maximum wire O.D., .38" (9.50mm).

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCM-67-99](#) [PCM-A-Z](#) [PCM-0](#) [PCM-GRY](#) [PCM-125-149](#) [PCM-100-124](#) [PCM-34-66](#) [PCM-1-33](#) [PCM-99](#) [PCM-1-18](#) [PCM-A](#) [PCM-L1](#) [PCM-ORN](#) [PCM-WHT](#) [PCM-YEL](#) [PCM-0-9](#) [PCM-150-174](#) [PCM-200-224](#) [PCM-225-249](#) [PCM-325-349](#) [PCM-400-424](#) [PCM-425-449](#) [PCM-1-4](#) [PCM-TAN](#) [PCM-1-6](#)