





DWG. NO.	031-1649		
REVISIONS			
SYM.	E.C.N.	DATE	APVD.
A	24536	3/12/01	
REVISED SILKSCREEN			



SPECIFICATIONS					
WIRING	INPUT		OUTPUT		
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD	
				MAX. AMPS	MAX. KVA
SINGLE PHASE	120	50/60	0-140	10	1.4

UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ±				UNITS		STACO ENERGY PRODUCTS CO. A Components Corporation of Ametec Company 301 Guadalupe Boulevard Dayton, Ohio 45403 USA							
DECIMALS	HOLES	ANGLES	DRAFT	IN [mm]									
.XX	.0000	.01	1°	ALL DIMENSIONS APPLY AFTER PLATING									
.XXX	.005		1-1/2°										
MATERIAL:													
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.						DRAWN BY		DATE	FIRST USED ON	DO NOT SCALE DWG.			
						S.A. SMITH		10/10/96	3PN1010BV				
						CHECKER		DATE	WEIGHT APPROX.		CAGE CODE	DWG. SIZE	DWG. NO.
									10.25 LBS		83008	D	031-1649
						ENGINEER		DATE	SCALE	SHEET			
									1=1	1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

[3PN1010BV](#)