




DRAWING MADE IN THIRD ANGLE PROJECTION

© COPYRIGHT 1981, 1982 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.



REVISIONS				
P	F	ZONE	DESCRIPTION	DATE
		L	REVISED PER ECO-15-008006	17NOV2015

USED WITH PART NUMBER	C DIM	B DIM	A SPACES	NUMBER OF POSITIONS	PART NUMBER
102791-7	1.830	1.600	16	34	1-102792-1
102791-5	3.120	2.900	29	61	1-102792-0
102791-1	1.430	1.200	12	26	-9
102791-2	.530	.300	3	8	-8
102791-3	.920	.700	7	16	102792-7
102791-1	.930	.200	2	6	102792-6
1-102791-0	1.130	.900	9	20	102792-5
102791-8	2.630	2.400	24	50	102792-4
102791-6	2.130	1.900	19	40	102792-3
102791-4	1.030	.800	8	18	102792-2
102791-2	.630	.400	4	10	102792-1

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.
TOLERANCES ON:
DECIMALS $\pm .005$
ANGLES $\pm .005$

MATERIAL 155-FLAME RETARDANT
THERMOPLASTIC COLOR-BLACK.
POSTS-COPPER ALLOY

FINISH
POSTS: .00050 GOLD IN CONTACT
AREA, GOLD FLASH ON
REMAINDER OF POST.
.00050 NICKEL UNDERPLATE

CONTRACT NO

DR

CHK

APPD

APPD

DSGN APPD

OTHER APPD

TE

TE Connectivity

NAME ASSEMBLY, HEADER,
AMPMODU, DOUBLE ROW .100 ϕ
RIGHT ANGLE

SIZE CODE IDENT NO DRAWING NO

C 00779

102792

SCALE 2-1

SHEET 1 OF 1

CUSTOMER DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[102792-1](#)