



Dimensions: In.

SPECIFICATIONS	
Material:	nylon 6/6
Temperature range:	-10°C to +85°C
Weather resistance:	UV resistance

Mouser Stock No.	Tensile Strength (Lbs)	L (In.)	Max. Bundle Dia. (In.)	W (In.)
481-0102UV	18	4.0	.980	.098
481-0108UV	40	6.0	1.54	.146
481-0115UV	50	8.0	2.17	.181

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eagle Plastic Devices:

[481-0108UV](#) [481-0115UV](#) [481-0102UV](#)