






2.5mm Mono Phone Jack

161-2505-E

KOBI CONN

2.5mm Mono Phone Jack



Dimensions: in.
(except where noted)

SPECIFICATIONS	
Type:	2.5mm, PCB mono phone
Contact resistance:	30mΩ max. @ 100mA
Insulation resistance:	100MΩ min. @ 500VDC
Solder Temperature:	220°C
Body material:	polyacetal (POM)
RoHS Compliant	

Date Last Revised: 12-17-07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301158

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-2505-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-2505-E](#)