


# NuPRO-E340

PICMG® 1.3 Full-Size LGA1155 Intel® Core™ i7/i5/i3/Pentium®/Celeron® Processor-based SHB



## Features

- 2nd Gen and 3rd Gen Intel® Core™ i7/i5/i3/Pentium®/Celeron® processor
- Intel® Q67 Express chipset supporting PCI Express 2.0
- Intel® Rapid Storage Technology, supports RAID 0/1/5/10
- 6x COM ports (including 1x RS-232/422/485/485+)
- Supports USB 3.0 with 5 Gb/s data transfer rate
- Supports Serial ATA with 6 Gb/s data transfer rate

## Specifications

### Processor & System

<b>CPU</b>	Intel® Core™ i7-3770, 3.4 GHz, 8M Cache, 22nm, 77W TDP, LGA1155 (4C) Intel® Core™ i7-2600, 3.4 GHz, 8M Cache, 32nm, 95W TDP, LGA1155 (4C) Intel® Core™ i5-3550S, 3.0 GHz, 6M Cache, 22nm, 65W TDP, LGA1155 (4C) Intel® Core™ i5-2400, 3.1 GHz, 6M Cache, 32nm, 95W TDP, LGA1155 (4C) Intel® Core™ i3-3220, 3.3 GHz, 3M Cache, 22nm, 55W TDP, LGA1155 (2C) Intel® Core™ i3-2120, 3.3 GHz, 3M Cache, 32nm, 65W TDP, LGA1155 (2C) Intel® Pentium® G2120, 3.1 GHz, 3M Cache, 22nm, 55W TDP, LGA1155 (2C) Intel® Pentium® G850, 2.9 GHz, 3M Cache, 32nm, 65W TDP, LGA1155 (2C) Intel® Celeron® G540, 2.5 GHz, 2M Cache, 22nm, 55W TDP, LGA1155 (2C)
<b>Chipset</b>	Intel® Q67 Express Chipset (Cougar Point)
<b>Memory</b>	2x 240-pin DIMM sockets Dual -channel DDR3 1333/1600MHz, up to 16 GB
<b>TPM</b>	Infineon SLB 9635 TT 1.2
<b>BIOS</b>	AMIBIOS 64 Mb SPI BIOS
<b>Watchdog Timer</b>	1-255 sec or 1-255 min software programmable, can generate system reset
<b>Hardware Monitor</b>	CPU/System temperature, fan speed and onboard DC voltages
<b>Operating Systems</b>	Windows® XP, 7 32/64-bit Fedora™ 14, Red Hat Enterprise Linux 5

## I/O Interfaces

<b>Serial ATA</b>	2x SATA 6 Gb/s ports 4x SATA 3 Gb/s ports Supports RAID 0/1/5/10
<b>PCI/PCIe Busses (via backplane)</b>	1x PCIe x16, Rev. 2.0 1x PCIe x4, Rev. 2.0 4x PCI 32-bit/33MHz
<b>USB</b>	2x USB 3.0 ports on faceplate 12x USB 2.0 ports (8x onboard pin headers and 4x backplane)
<b>KB/MS</b>	1x internal pin header for PS/2 keyboard/mouse
<b>Parallel Port</b>	1x LPT
<b>Serial Port</b>	5x RS-232, 1x RS-232/422/485/485+

## Audio

<b>Audio Codec</b>	Realtek ALC262 support by DB-Audio2 daughter board
<b>Interface</b>	Pin header for High Definition Audio interface

## Display

<b>Graphics</b>	Integrated Intel® HD Graphics
<b>VGA</b>	Resolutions up to 2048 x 1536 @ 75 Hz
<b>DVI</b>	1x internal pin header for DVI-D output

## Ethernet

<b>Controller</b>	Intel® 82579LM Gigabit Ethernet PHY Intel® 82574L Gigabit Ethernet Controller
<b>Interface</b>	PCIe x1 bus
<b>iAMT</b>	Supports Intel® AMT 7.0
<b>Wake On LAN</b>	Support on LAN1

## Mechanical and Environmental

<b>Form Factor</b>	Full-Size PICMG® 1.3 System Host Board
<b>Dimensions</b>	338 mm x 126 mm (L x W)
<b>Operating Temp.</b>	0°C to 60°C
<b>Storage Temp.</b>	-20°C to 80°C
<b>Certifications</b>	CE, FCC Class A
<b>Relative Humidity</b>	10% to 90%, non-condensing

## Ordering Information

Model Number	Description/Configuration
NuPRO-E340	PICMG® 1.3 Full-Size LGA1155 Intel® Core™ i7/i5/i3/Pentium®/Celeron® Processor-based SHB

Note: CPU, Memory module and Cooler kit are not included.

## Optional Accessories

Model Number	Description/Configuration
LGA1156 1U CPU Cooler	LGA1156 1U Thermal Module
LGA1156 2U CPU Cooler	LGA1156 2U Thermal Module
LGA1156 3U CPU Cooler	LGA1156 3U Thermal Module
DB-Audio2	High Definition Audio daughter board with Mic-in/Line-in/Line-out
DVI cable with bracket	
LPT cable with bracket	
PS/2 cable with bracket for keyboard/mouse	

## Packing List

NuPRO-E340	1x 2-port USB 2.0 cable with bracket
2x SATA data cable	3x 2-port COM cables with bracket
User's manual	Driver DVD

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADLINK Technology:](#)

[NuPRO-E340](#)