

Battery Powered Milliohm Meter

High accuracy, high resolution portable Milliohm Meter
Battery operated for field use

Features:

- Four terminal Kelvin measurements
- Over-temperature and over-voltage protection
- 5 ranges with 100μ max resolution
- Large 2000 count LCD display
- Auto-Hold and Auto power off
- Invalid test indicators prevent inaccurate measurements
- Built-in water resistant case with shoulder strap
- Complete with 8AA batteries, and 2 sets of test leads (4 wire with 4 alligator clips and 4 wire with 2 Kelvin alligator clips)



Kelvin alligator clips

Specifications	Range	Resolution	Current	Basic Accuracy
Resistance	200.0m	0.1m	100mA	±(0.5%rdg +2 digits)
	2000m	1m	100mA	±(0.5%rdg +2 digits)
	20.00	0.01	10mA	±(0.5%rdg +2 digits)
	200.0	0.1	10mA	±(0.5%rdg +2 digits)
	2000	1	1mA	±(0.5%rdg +2 digits)
Power	8 AA batteries			
Dimensions	9.8 x 7.5 x 4.3" (250 x 190 x 110mm)			
Weight	3.3lbs (1.5kg)			

Ordering Information:

380580.....Battery Powered Milliohm Meter
380580-NIST380580 with Calibration Traceable to NIST
380565.....Test Leads w/Kelvin clips for 380580



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Extech:

[380580](#) [380580-NIST](#) [380565](#)