



5		1			<div>UNLESS OTHERWISE SPECIFIED</div> <div>1.REMOVE ALL BURRS. 2.BREAK ALL CONNERS & EDGES CO.15 MAX. 3.CHAMFER 1ST & LAST THREADS 45°. 4.DIAMETERS ON COMMON CENTERS. 5.TOE OF CONCENTRIC WITHIN 0.1 I.R. 6.ALL DIMENSIONS ARE AFTER PLATING.</div>	<div>* MAJOR DIMENSION</div> <div>UNLESS OTHERWISE NOTED TOLERANCES 0.5-6=±0.2 6-30=±0.4 30-120=±0.6 120-315=±1.0 ANGLES=±1°</div>				APPROVED		<div>Bomar Interconnect Products, Inc.</div> <div>TITLE Lock Washer 364 Series</div> <div>DRAWING NO. 364LW</div> <div>REV A</div>			
4		1								CHECKED					
3		1								B.Foster					
2		1													
1	Body	1	Brass	Nickel							SCALE	3/1	UNIT	MM	DRAWN DATE 05/29/03
10	Description	Q'ty	Material	Finish											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[364LW](#)