

# MANO873

Mini-ITX SBC with LGA1155 Socket 3rd Gen Intel® Core™ Processor, Intel® Q77, VGA/DVI-D, Dual LANs and USB 3.0

## Features

- LGA1155 socket 3rd gen Intel® Core™ i7/i5/i3 & Celeron® processors
- 2 DDR3-1333/1600 SO-DIMM, up to 16GB
- PCIe x16 Gen3 supported
- 2 SATA-600 and 2 SATA-300 with RAID 0/1/5/10
- 4 USB 3.0
- Intel® AMT 8.0 supported
- TPM 1.2 supported
- mSATA supported





### Core System

CPU	LGA1155 socket 3rd gen Intel® Core™ i7/i5/i3 & Celeron® processor
System Memory	2 x 204-pin DDR3-1333/1600 SO-DIMM dual channel, up to 16GB
Chipset	Intel® Q77
BIOS	AMI UEFI BIOS with OA 3.0 built
SSD	N/A
Watchdog Timer	255 level, 1 ~ 255 sec
Expansion Interface	1 x PCIe x16 Gen3 1 x PCI Express Mini Card slot (shared mSATA)
Battery	Lithium 3V/220 mAh
Power Requirements	i7-2700K: +5V @ 1.8A, +12V @ 6.1A, +5VSB @ 0.3A, +3.3V @ 0.9A
Size	170 x 170 mm
Board Thickness	1.6 mm
Temperature	0°C ~ +60°C (+32°F ~ +140°F), operation
Operation Humidity	10% ~ 95% relative humidity, non-condensing

### I/O

MIO	1 x RS-232/422/485 (COM 1); with 5V/12V power 1 x RS-232 (COM 2) 1 x PS/2 keyboard & mouse
SATA	2 x SATA-300; 1 SATA-300 supports SATA DOM 2 x SATA-600, support RAID 0/1/5/10
Hardware Monitoring	Detect CPU/System temperature, voltage and fan speed
Ethernet	1st port as 10/100/1000 Mbps support WOL, PXE with Intel® 82579LM/V (LAN 1) 2nd port as 10/100/1000 Mbps support WOL, PXE with Intel® 82583V (LAN 2)
Audio	HD Audio as Mic-in/Line-out with Realtek ALC662
USB	4 x USB 3.0 (2 USB 3.0 from Intel® Q77; 2 USB 3.0 from Renesas uPD720202 with WinXP driver) 4 x USB 2.0
TPM	Infineon TPM1.2 SLB9635
Digital I/O	8 channels (4-in & 4-out)
SM BUS	N/A



### Display

Chipset	Intel® HD 2000/3000/4000 graphics
Memory Size	Shared memory
Display Interface	1 x VGA 1 x DVI-D

### Packing List

<b>Standard</b>	User's manual/utility CD, cable, I/O bracket
-----------------	--

### Ordering Information

<b>Standard</b>	MANO873V/GGA (P/N: E38M873101)	Mini ITX SBC with LGA1155 socket 3rd gen Intel® Core™ i7/i5/i3 & Celeron®, VGA/DVI-D, 2 GbE LANs and USB 3.0
<b>Optional</b>	5077L07C000E	LGA115x 1U fan back plate H:2.45 mm
	50721127100E	LGA115x 1.5U fan JAC6L23C-C H=35



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[MANO873VGGA](#)