Tip Jacks
Insulated Standard: Rib-Loc® Type

INCHES (MILLIMETERS)
CUSTOMER DRAWINGS AVAILABLE UPON REQUEST

SPECIFICATIONS
Contact: Brass body per QQ-B-626D with wrap around beryllium copper spring per QQ-C-553
Finish: Silver
Body: Nylon 6/6 per ASTM D4066
Panel Thickness: Up to .375 (9.05)

RATINGS
Current: 5 amps
Breakdown Voltage: 3500 Vrms minimum
Contact Resistance: 0.005 ohms maximum
Adjacent Jack C: 1 pF nominal

SILVER PLATING	
105-1044-001	Green



MOUNTING HOLE OPTIONS

For Standard Tip Plug: .080 (2.00) Diameter
FEATURES:
- Machined contact with turret terminal
- Installs by pressing into mounting hole, no mounting hardware required
- Closed entry blocks access or probes greater than .085 (2.16)
- Nylon UL approved for self extinguishing

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cinch Connectivity Solutions:

105-1044-001