





PRODUCT NUMBER
SEE SHEET 2



NOTES :

1. MINI PUSH-OUT FORCE TERMINAL IN BOTH DIRECTIONS 22N.
2. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
EXAMPLE: 8 POS: (Nx2.54)-1=19.32 mm



| | | | | | | | | | |
|--------------------------|----------|-----------------------|----------|---------------------------------------|-----------|------------------|----------|------------------------------------|--|
| mat'l. code SEE NOTES | | surface ISO 1302 ✓ | | tolerance ISO 406 ISO 1101 | | projection mm | | product family DUBOX | |
| ltr | ecn no | dr | date | tolerances unless otherwise specified | | mm | | title SHR. HEADER STR DR TMT | |
| P | F07-0220 | JCO | 07.06.14 | angles | Linear | .X | ±0.3 | scale 5:1 | |
| R | F08-0147 | YOV | 08.04.14 | | | .XX | ±0.15 | dwg no 76385 | |
| S | B-19286 | AMA | 14.11.03 | | | .XXX | ±0.05 | sheet 1 of 2 size A3 | |
| T | B-21014 | BVE | 15.06.01 | dr | G CORBOZ | | 01.01.12 | type CUSTOMER Drawing | |
| | | | | enr | P NIZZI | | 01.01.12 | | |
| M | F06-0228 | LMU | 06.07.11 | chr | D LEGRAND | | 01.01.12 | | |
| N | F07-0147 | LMU | 07.03.01 | appd | P N | | 01.01.12 | | |
| sheet | revision | T | G | | | | | | |
| index | sheet | 1 | 2 | | | | | | |



Copyright FCI

RoHS COMPLIANT PRODUCT NUMBER

76385-YXXLF

PLATING CODE

RoHS COMPLIANT, SEE NOTE 5

3= 0.76µm GOLD/GXT ON CONTACT AREA.

2µm MIN MATTE TIN ON TAILS.

4= 2µm MIN MATTE TIN FULL PLATED

NUMBER OF POSITIONS PER ROW: 02 TO 18

1.27µm Ni MIN UNDERPLATING

NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-O COLOR: BLACK.
- 2 - TERMINAL MATERIAL: COPPER ALLOY.
- 3 - 2 UP TO 6 POSITIONS PER ROW, PRODUCT PACKED IN PLASTIC BAG.
7 UP TO 18 POSITIONS PER ROW, PRODUCT PACKED IN TUBE.
- 4 - ONLY DASH NUMBER -X02 AND -X03
ALWAYS TEN (10) PRODUCTS MOLDED ASSEMBLY
& DELIVERED TON STRIP ACCORDING PHANTOM LINES.
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004

| | | | | | | | | | |
|-------------|----------|------------|----------|---------------------------------------|-------------|------------|--|------------------|--|
| mat'l. code | | surface | | tolerance | | projection | | product family | |
| SEE NOTES | | ISO 1302 ✓ | | ISO 406 ISO 1101 | | | | DUBOX | |
| ltr | ecn no | dr | date | tolerances unless otherwise specified | | | | title | |
| | | | | angles | linear | | | SHR. HEADER | |
| B | F06-0106 | LMU | 06.01.12 | | .X ±0.3 | | | STR DR TMT | |
| C | F06-0228 | LMU | 06.07.11 | | .XX ±0.15 | scale 5:1 | | | |
| D | F07-0147 | LMU | 07.03.01 | dr | L.MULIN | 05.03.31 | | dwg no | |
| E | F07-0220 | JCO | 07.06.14 | engr | J.COMPAGNON | 05.03.31 | | sheet 2 of | |
| F | F08-0147 | YOV | 08.04.14 | chr | | | | 76385 | |
| G | B-19286 | AMA | 14.11.03 | appd | JM.C | 05.03.31 | | size | |
| sheet | | revision | | | | | | A3 | |
| index | | sheet | | | | | | type | |
| | | | | | | | | CUSTOMER Drawing | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[76385-311LF](#)