



MATERIALS:

Banana Plug Springs: Beryllium Copper, Cond. H.T.

Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches

Banana Plug Bodies and Solder Turret Terminals: Brass, Alloy 360 ½ Hard.

Finish: Nickel plated per QQ-N-290 Class 2 (200/300 microinches)

Molded Housing: Electrical grade Phenolic. Color: Black

Marking: "MODEL 2096 POMONA ELECTRONICS CALIF."

Cover: Phenolic Plate. Color: Black

Screws: 2 ea. #2-56 x (3/16") Pan HD. - Steel

RATINGS:

Operating Temperature: +150°C. (+302°F.) Max.

Current: 15 Amperes

ORDERING INFORMATION: Model 2096

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[2096](#)