

20 Degree Slope Welded Steel Console Rack *1564 Series*

Modular - Unassembled




Features

- Constructed in 14-gauge steel (frame) and 14-gauge steel (rails).
- Choice of two depths 24.5", 31.5" usable depth.
- Sloped panel height of 17.5" (10 U).
- Front panel height of 26.25" (15U).
- Finished in textured beige powder paint (body) and textured black powder paint (mounting rails).
- Tested to nearly double the suggested load rating of 600 lbs.
- RoHS Compliant.
- Manufactured in North America.

Unit is Shipped Complete with

- One (1) Pair of removable side panels
- Two (2) pairs of EIA-310-D compliant pre-installed upper round hole punched mounting rails
- Two (2) pairs of EIA-310-D compliant pre-installed lower round hole punched mounting rails
- One (1) Set of four (4) leveling feet

Gallery



Accessories

[Shelves](#)

[Rack Panels](#)

[Lite Duty Caster Set](#)

[Cooling](#)


[Outlet Strips](#)

[Cable Management](#)

[Round Hole Punched Combination](#)

[Mounting Rails](#)

[Mounting Hardware](#)



1564 Frame and Side Panels

Frame	Overall Dimensions						Side Panel
Part No.	A	B	C	D	E	F	Part No.
1564A2BK1	22.56	24.50	19.06	14.00	17.50	21.31	1564APBK1
1564B2BK1	22.56	31.50	19.06	21.00	24.50	19.56	1564BPBK1

Side Panels Sold in Pairs

1564 Doors

Door Type	Front Door Part No.	Front Door with Desk Unit Option Part No.	Rear Door Part No.
Solid	RSDF19026BK1	RSDF19042BK1	RSDF19042BK1
Louvered	RSDL19026BK1	RSDL19042BK1	RSDL19042BK1

Doors are constructed of 18 gauge steel and feature lockable latch.

1564 Top Panels

Part No.	Top Panel	For Use With Frames
PBRs19014BK2	Solid	1564A2
PBRs19021BK2	Solid	1564B2
PVLK19014BK1	Louvered	1564A2
PVLK19021BK1	Louvered	1564B2

1564 Corner Wedges

Part No.	For Use With Frame
1564AW30BK1	1564A2
1564BW30BK1	1564B2
1564AW60BK1	1564A2
1564BW60BK1	1564B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hammond:

[PBR19021CG2](#) [PBR19021BK2](#) [PBR19014CG2](#) [PBR19014BK2](#)