





PART NUMBER
10124234-060003LF



ITEM NO.	DESCRIPTION	Q'TY
1	HOUSING, THERMOPLASTIC RESIN, UL94V-0	1
2	MATING CONTACT, HIGH CONDUCTIVITY COPPER ALLOY, TIN PLATED.	2
3	FLAT CONTACT, THROUGH HOLE PITCH=18.00mm HIGH CONDUCTIVITY COPPER ALLOY TIN PLATED	1
4	FLAT CONTACT, THROUGH HOLE PITCH=16.50mm HIGH CONDUCTIVITY COPPER ALLOY TIN PLATED	1
5	FLEXIBLE POWER WIRE, 6 AWG, UL RECONGIZED, 105°C, 600V RED INSULATION COLOR, LEGTH=90mm (INSULATION ONLY)	1
6	FLEXIBLE POWER WIRE, 6 AWG, UL RECONGIZED, 105°C, 600V BLACK INSULATION COLOR, LEGTH=90mm (INSULATION ONLY)	1
7	THERMAL SHRINKAGE TUBING, COLOR BLACK, 0.5mm THICKNESS. LENGTH 25mm MIN.	4

NOTES:
(1) ELECTRICAL RATING: 600V, 60A
(2) WORKING TEMPERATURE: -20~75°C
(3) REFERENCE DOCUMENTS:
PRODUCT SPECIFICATION: FCI-GS-12-1127
PACKAGEING SPECIFICATION: FCI-GS-14-2295
(4) RoHS COMPLIANT.



spec ref	dr	Beer Fu	2013-02-01	projection	MM	size	A3	scale	1:1
tolerance std	eng	Beer Fu	2013-02-01	chr	Beer Fu	2013-02-01	ecn no	rel level	RELEASED
	appr	Beer Fu	2013-02-01	product family	-	rel level	RELEASED		
surface	linear	0.X	±0.30	FCI	POWER CABLE	dwg no	10124234-060003LF	rev	A
		0.XX	±0.15	www.fci.com	FINAL ASSEMBLY				
		0.XXX	±0.05						
	angular	0°	±5°						
				cat. no.	-	CUSTOMER	sheet 1 of 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10124234-060003LF](#)