





REV.	DATE	DESCRIPTION
A	03/06/05	UPDATE DRAWING FORMAT AND PART NO.



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: D.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex				
8						DRAWN	G.R.S.					03/06/05
7						CHECKED			PART DESCRIPTION SMA STRAIGHT PLUG – REV. POLARITY (FOR .141" SEMI RIGID CABLE)			
6						ISSUED						
5						SHEET	1 OF 1		PART NO. 132102RP			
4												
3	CONTACT PIN	BRASS	GOLD	1				DWG. NO. 132102RP.DWG				
2	INSULATOR	TEFLON	NATURAL	1	CAD FILE C:/132/132102RP.DWG							REV. A
1	BODY	BRASS	GOLD	1								
	DESCRIPTION	MATERIAL	FINISH	QTY								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[132102RP](#)