

HEYCO






Heyco® Original Series-35 Liquid Tight Cordgrips Pigtail, NPT Hubs

- Flexible Pigtail™ extender prevents sharp bends and extends cable life.
- IP 68 rated.
- Widest range of approved cable diameters.
- For use in clearance or threaded holes.
- Acme threads on body prevent skipping and speed installation.
- All nylon construction with TPE sealing gland resists salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL.)
- Multiple sizes for flexible cord diameters ranging from .069" (1,8 mm) to .709" (18,0 mm).
- We recommend using the fitting with the smallest maximum diameter that will fit your application.
- **Locknuts not included.** For nylon locknut specifications or to order locknuts separately, see page 3-29.
- For Heyco Liquid Tight Threaded Plugs, see page 3-32.
- Consult Heyco for cordgrips molded in other colors.

CABLE DIA. RANGE				PART NO.		DESCRIPTION	UL or	PART DIMENSIONS									
Minimum		Maximum		Black	Gray			A Clearance Hole Dia.		B Max. O.A. Length		C Thread Length		D Wrenching Nut Thk.		E Wrenching Nut Flat Size	
in.	mm.	in.	mm.					in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
.069	1,8	.187	4,7	3474	3475	FLEX RLTF 3/8	UL	.670	17,0	2.97	75,4	.53	13,5	.20	5,1	.75	19,1
.181	4,6	.312	7,9	3254	3255	FLEX LTF 3/8											
.170	4,3	.470	11,9	3251	3252	FLEX LTF 1/2	UL	.875	22,2	4.09	103,9	.62	15,7	.20	5,1	.95	24,1
.230	5,8	.546	13,9	3266	3267	FLEX LTF LL 1/2	UL	.875	22,2	4.54	115,3	.62	15,7	.23	5,8	1.05	26,7
.250	6,4	.485	12,3	3462	3463	FLEX RLTF 3/4	UL	1.068	27,1	5.14	130,6	.63	16,0	.23	5,8	1.30	33,0
.450	11,4	.709	18,0	3239	3242	FLEX LTF 3/4											

Standard colors black and gray.



SUGGESTED CLEARANCE HOLE FOR NONTHEADED MOUNTING

*Quick
Specs*

Material
Certifications



Nylon 6/6 w/TPE Sealing Gland
Listed under Underwriters' Laboratories File E51579
Recognized under the Component Program of Underwriters' Laboratories File E51579
Certified by Canadian Standards Association File 93876C

Flammability Rating
Temperature Rating

94V-2
Static -40°F (-40°C) to 239°F (115°C)
Dynamic -4°F (-20°C) to 212°F (100°C)

IP Rating

IP 68 (70 PSI, 5 BAR)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3833](#) [3837](#) [3834](#) [3830](#) [3831](#) [3832](#)