



Heyco® Nylon PCB Supports - Imperial Spacing

BAYONET SNAP LOCK 8,7 / ARROWHEAD SNAP LOCK HLSP9	BAYONET SNAP FIT 10,2 / WINGED TWO PRONG SNAP LOCK HLSP10	BAYONET SNAP LOCK 8,7 / TWO PRONG SNAP LOCK HLSP11	BAYONET SNAP LOCK 8,7 / TEARDROP SNAP LOCK HTLSP
--	--	---	---

		Maximum Thickness		Mounting Hole Diameter		Maximum Thickness		Mounting Hole Diameter		Maximum Thickness		Mounting Hole Diameter		Maximum Thickness		Mounting Hole Diameter	
		in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
PCB		.062	1,6	.125	3,2	.062	1,6	.157	4,0	.062	1,6	.125	3,2	.062	1,6	.098	2,5
Chassis		.078	2,0	.125	3,2	.078	2,0	.187	4,8	.062	1,6	.125	3,2	.062	1,6	.125	3,2
A		PART NO.		DESCRIPTION		PART NO.		DESCRIPTION		PART NO.		DESCRIPTION		PART NO.		DESCRIPTION	
in.	mm.	Natural				Natural				Natural				Natural			
.125	3,2	10160		HLSP9-02						10178		HLSP11-02		10190		HTLSP-02	
.187	4,8	10161		HLSP9-03		10170		HLSP10-03		10179		HLSP11-03		10191		HTLSP-03	
.250	6,4	10162		HLSP9-04		10171		HLSP10-04		10180		HLSP11-04		10192		HTLSP-04	
.312	7,9	10163		HLSP9-05						10181		HLSP11-05		10193		HTLSP-05	
.375	9,5	10164		HLSP9-06		10172		HLSP10-06		10182		HLSP11-06		10194		HTLSP-06	
.437	11,1	10165		HLSP9-07						10183		HLSP11-07		10195		HTLSP-07	
.500	12,7	10166		HLSP9-08		10173		HLSP10-08		10184		HLSP11-08		10196		HTLSP-08	
.562	14,3	10167		HLSP9-09						10185		HLSP11-09					
.625	15,9	10168		HLSP9-10		10174		HLSP10-10		10186		HLSP11-10		10197		HTLSP-10	
.750	19,1					10175		HLSP10-12		10187		HLSP11-12					
.875	22,2					10176		HLSP10-14		10188		HLSP11-14					

Standard color natural. For special order parts in UL 94V-0 natural material, add the suffix "F" to Part No.

Material Nylon 6/6
Flammability Rating 94V-2
Temperature Range .4°F (-18°C) to 185°F (85°C)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[10170F](#) [10176F](#) [10168F](#) [10172F](#) [10188F](#) [10162F](#) [10179F](#) [10160F](#) [10190F](#) [10178F](#) [10196F](#) [10192F](#) [10193F](#)
[10183F](#) [10191F](#) [10180F](#) [10182F](#) [10194F](#) [10185F](#) [10197F](#) [10186F](#) [10171F](#) [10184F](#) [10175F](#) [10164F](#) [10163F](#)
[10173F](#) [10165F](#) [10181F](#) [10161F](#) [10195F](#) [10166F](#) [10187F](#) [10174F](#) [10167F](#)