



CATALOG LISTING  
924CE16-T3

FED. MFG. CODE 91929



CIRCUIT DIAGRAM



- NOTES  
1 - ZINC HOUSING FINISHED WITH GRAY PAINT  
2 - SWITCH WILL ACTUATE IN BOTH DIRECTIONS  
3 - MAKE BEFORE BREAK CIRCUITRY

924CE16-T3



DRAWING  
NUMBER

2

|           |          |
|-----------|----------|
| REVISIONS |          |
| A         | CO-69061 |
| S A V     |          |
| 4 NOV 91  |          |

|             |          |          |
|-------------|----------|----------|
| RELEASE NO. | PR-14729 | REPLACES |
|-------------|----------|----------|

**CHECK**

CHECK

CHECK

91

NC

AV

DDM/CAD

2X Ø .200±.010 -  
MOUNTING HOLES  
(Ø .40 C'BORE  
.24 DEEP)

—P.V.C. SHEATHED CABLE  
18/5 S.J.T.O.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

## CHARACTERISTICS

|                 |           |                 |
|-----------------|-----------|-----------------|
| OPERATING FORCE | — — — — — | 2.62 IN. LB MAX |
| PRETRAVEL       | — — — — — | 48° MAX         |
| TOTAL TRAVEL    | — — — — — | 65° MIN         |
| MAKE TO BREAK   | — — — — — | 7° ± 6°         |


## ELECTRICAL DATA

CONTACT ARRANGEMENT  
S P D T D B

10A 250 VAC  
1/3 HP 125 OR 250 VAC



THIRD ANGLE PROJECTION



|       |      |
|-------|------|
| SCALE | FULL |
|-------|------|

DO NOT SCALE PRINT

**UNLESS OTHERWISE SPECIFIED  
TOLERANCES ARE**

|             |        |            |
|-------------|--------|------------|
| ONE PLACE   | (.01)  | $\pm .030$ |
| TWO PLACE   | (.00)  | $\pm .015$ |
| THREE PLACE | (.000) | $\pm .005$ |
| ANGLES      |        | $\pm$      |

WEIGHT

ANSI Y14.5M-1982 APPLIES

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[924CE16-T3](#)