




NOTES:

1. GLASS ENVELOPE TO BE TIPLESS AND SEAMLESS.
2. BASE MATERIAL: BRASS, NICKEL PLATED.
3. LAMPS TO BE 100% AGED FOR EQUIVALENT OF TEN HOURS AT RATED VOLTAGE.
4. LAMPS TO BE DIESUNK WITH "JKL" AND NUMBER (EX: JKL 8270).
5. FINAL INSPECTION PER MIL. STD. 105D TO AN AQL OF 2.5 (NOTE: AS15 AND AS10 LAMPS WILL BE 100% INSPECTED FOR MSCP AND AMPERAGE).

JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
8102	1.5	.075	.030	0.38	16,000	C-2R
CF23	5.0	.020	.020	0.25	50,000	C-2R
8022	5.0	.021	.034	0.43	10,000	C-2R
7234	5.0	.030	.030	0.38	16,000	C-2R
682	5.0	.060	.030	0.38	100,000	C-2R
685	5.0	.060	.050	0.63	100,000	C-2R
6180	5.0	.060	.150	1.89	5,000	C-2R
714	5.0	.075	.090	1.13	25,000	C-2R
718	5.0	.115	.150	1.89	40,000	C-2R
7240	10.0	.027	.100	1.26	10,000	C-2F
32	12.0	.060	.150	1.89	16,000	C-2F
22	14.0	.040	.150	1.89	16,000	C-2F
8112	14.0	.065	.150	1.89	16,000	C-2F
7241	18.0	.026	.150	1.89	16,000	C-2F
CF16	28.0	.016	.025	0.31	16,000	C-2F
6839	28.0	.024	.150	1.89	16,000	CC-2F

THIRD ANGLE PROJECTION			METRIC DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0		JKL COMPONENTS CORPORATION																			
			DRAWN BY L. WENGSTROM		APPV'D BY BW		DATE 4/5/00		TITLE T-1 STANDARD MIDGET FLANGE															
RELEASE & CANCEL 7247, 7231, 7232, CF43, 7250, CF30, CF44, CF45,			4/5/00		SIZE A		FSCM NO. 55335		DRAWING NO.		FLANGE T-1													
REV. NO.			DESCRIPTION/ECO NUMBER			APPV'D DATE			- CAD DRAWING -			MANUAL REVISIONS NOT PERMITTED			SCALE NONE		RELEASED DATE 4/5/00		REVISION DATE		REV. NO.		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[6180](#) [6839](#) [8112](#) [682](#) [685](#) [714](#) [7234](#) [7240](#) [8022](#) [22](#) [8102](#)