

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0009507041](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK 3.96mm Crimp Terminal Housing, 4 Circuits, Natural](#)

Documents:

[3D Model](#) [Packaging Specification PK-2139-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-08-50-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [2139](#)
 Application Power, Wire-to-Board
 Overview [KK® Interconnect System - Molex](#)
 Product Name KK 396
 UPC 800753531505

Physical

Circuits (maximum) 4
 Color - Resin Natural
 Flammability 94V-2
 Gender Receptacle
 Glow-Wire Capable No
 Material - Resin Nylon
 Net Weight 1.024/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 3.96mm
 Temperature Range - Operating See Product Specification

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Engineering Number 2139-4C

Reference - Drawing Numbers

Packaging Specification PK-2139-001-001
 Product Specification PS-08-50-001
 Sales Drawing SD-2139



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[2139](#) Series

Mates With

KK 396 Headers: [41771](#) , [41772](#) , [41791](#) ,
[41792](#) , [42491](#) , [42492](#) , KK 396 Breakaway
 Headers: [41661](#) , [41662](#) , [41671](#) , [41672](#)

Use With

[2478](#) Crimp Terminals for 18-24 AWG, [2578](#)
 Crimp Terminals for 22-26 AWG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[09-50-7041](#)