

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0009508103
Status: Active
Overview: KK Interconnect Solutions
Description: KK 3.96mm Crimp Terminal Housing, Friction Ramp, 10 Circuits, Natural

Documents:
3D Model Product Specification PS-08-50-001 (PDF)
3D Model (PDF) RoHS Certificate of Compliance (PDF)
Drawing (PDF)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series 41695
Application Power, Wire-to-Board
Overview KK Interconnect Solutions
Product Name KK 396
UPC 800754227926

Physical

Breakaway No
Circuits (maximum) 10
Color - Resin Natural
Flammability 94V-0
Gender Receptacle
Glow-Wire Capable No
Keying to Mating Part None
Lock to Mating Part Yes
Material - Resin Polyester
Net Weight 3.365/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.96mm
Polarized to Mating Part Yes
Temperature Range - Operating See Product Specification

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 41695-N-D10

Reference - Drawing Numbers

Product Specification PS-08-50-001
Sales Drawing SD-41695-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

41695 Series

Mates With

KK 396 Header 41791 , 41792 , 41671 ,
41672 , 41661 , 41662

Use With

KK 396 Crimp Terminals 2478 , 2578 , 6838
, 7258 , 45570
L1NK 396 Pre-Crimped
Lead 797582145 , 797582146

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[09-50-8103](#)