

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0082285715

Status:

Active

Description:

1.27mm Pitch Round Conductor Flat Cable - 28 AWG (7 x 36) Stranded Tinned, 15 Circuits, Reel 30.48m Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable
Series	6800
Crimp Quality Equipment	Yes
Geographic Area	Asia
Product Name	Ribbon
UPC	800755001303
Physical	
Cable Length	30.48m
Circuits (Loaded)	15
Circuits (maximum)	15
Insulation	PVC
Packaging Type	Reel
Pitch - Termination Interface	1.27mm
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	28
Wire/Cable Type	(7x36) Stranded, Tinned
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	300V
Material Info	
Engineering Number	6800-15-100B
Reference - Drawing Numbers	
Sales Drawing	SD-6800-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Not Reviewed

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

6800 Series

Use With

70121 MX-50 Slimline Ribbon Cable. 90584 Picoflex PF-50 IDT Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[82-28-5715](#)