

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0152670793
Status: Active
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 76.00mm Cable Length, Tin (Sn) Plating, 11 Circuits

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification PS-15267-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Cable
Series 15267
Comments Contacts on the same side, Type A
Crimp Quality Equipment Yes
Overview FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Product Name Premo-Flex FFC Jumper
UPC 884982425811

Physical

Cable Length 76.00mm
Circuits (Loaded) 11
Contact Layout Type A (same side)
Material - Plating Mating Tin
Packaging Type Bag
Pitch - Mating Interface 1.00mm
Temperature Range - Operating -40° to +105°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical

Current - Maximum per Contact 1.2A
Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers

Product Specification PS-15267-001-001
Sales Drawing SD-15267-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series

15267 Series

Mates With

Easy-On FFC/FPC Connector:

522071133 , 522711179 , 526101133 ,
526101134

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15267-0793](#)