

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [48025-2090](#)
Status: **Active**
Overview: Magnetic Modular Jacks
Description: Modular Jack, Right Angle, 10/100, with Integrated Magnetic and LED, 8/8, without Ground Shield, Lead-Free

Documents:

[3D Model](#) [Test Summary TS-48025-010 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-48025-005 \(PDF\)](#)

Agency Certification


CSA LR19980
 UL E107635

General

Product Family Modular Jacks/Plugs
 Series [48025](#)
 Comments With LED|Without Ground Shield
 Component Type PCB Jack
 Magnetic Yes
 Overview [Magnetic Modular Jacks](#)
 Performance Category 5, 5e
 Power over Ethernet (PoE) Non-PoE
 Product Name Magnetic Jack
 UPC 822350848008

Physical

Boot Color N/A
 Color - Resin Black
 Durability (mating cycles max) 750
 Flammability 94V-0
 Inverted / Top Latch Yes
 Jack Height 12.60mm
 Keying to Mating Part Yes
 Lightpipes/LEDs LEDs
 Material - Metal Phosphor Bronze
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin Nylon
 Net Weight 4.980/g
 Orientation Right Angle (Side Entry)
 PCB Locator Yes
 PCB Retention Yes
 PCB Thickness - Recommended 1.60mm
 Packaging Type Tray
 Pitch - Mating Interface 1.02mm
 Pitch - Termination Interface 1.27mm
 Ports 1
 Positions / Loaded Contacts 8/8
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -40°C to +70°C
 Termination Interface: Style Through Hole
 Waterproof / Dustproof No
 Wire/Cable Type N/A



EU RoHS

**ELV and RoHS
 Compliant**
REACH SVHC
 Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[48025Series](#)

Mates With

FCC 68 Plugs

Electrical

| | |
|-------------------------------|----------------------|
| Current - Maximum per Contact | 1.5A |
| Grounding to PCB | Yes |
| Grounding to Panel | No Panel Ground Tabs |
| Shielded | Yes |
| Voltage - Maximum | 150V AC (RMS) |

Material Info**Reference - Drawing Numbers**

| | |
|-----------------------|--------------|
| Product Specification | PS-48025-005 |
| Sales Drawing | SD-48025-010 |
| Test Summary | TS-48025-010 |

This document was generated on 12/17/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[48025-2090](#)