

VOLTAGE CONTROLLED TEMPERATURE COMPENSATED CRYSTAL OSCILLATOR



5.0 X 3.2 X 1.5mm

ASVTX-09



FEATURES:

- Compact and low in height.
- Low current consumption.
- Suitable for high-density SMT.
- Vc function corresponds to PLL circuits.
- IR reflow possible.

APPLICATIONS:

- Cellular and cordless phones.
- Standard OSC for exact equipment.
- Mobile communication equipment.
- Portable radio equipment and music player.

STANDARD SPECIFICATIONS:

PARAMETERS

ABRACON P/N	ASVTX-09
Frequency	10.000MHz to 44.545MHz
Standard Frequencies	12.8MHz, 13.0MHz, 14.4MHz, 15.36MHz, 16.000MHz, 16.384MHz, 16.8MHz, 19.2MHz, 19.440MHz, 19.680MHz, 19.8MHz, 26.0MHz
Operating Temperature	- 30° C to + 75° C (See Table 1 for options)
Storage Temperature	- 40° C to + 85° C
Freq. Stability vs. +25°C vs. Operating Temp. vs. Aging vs. Supply Voltage vs. Load	± 0.5ppm standard (See option) ±2.5ppm standard (See Table1 for options) ± 1ppm/1st year ±0.2ppm (± 5% change) ±0.2ppm (± 10% change)
Voltage Control Range (Vcc)	1.5V ±1.0V standard (See options)
Supply Voltage (Vdd)	3.0V ± 5% Standard (See options)
Supply Current	2mA max
Output Type	Clipped Sine
Output Voltage	0.8Vp-p min
Output Load	10 kohm // 10 pF
Pullability	± 8ppm min
Transfer Function	Positive
Phase Noise	-110dBc/Hz @ 100KHz offset; -130dBc/Hz @ 1KHz offset

OPTIONS & PART IDENTIFICATION:

(Left blank if standard)

ASVTX - 09 - □ - Frequency - □ - □□□ - □

	Supply Voltage (Vdd)	Control Voltage (Vcc)	Frequency Stability vs +25° C	
A	2.5V±5%	1.25V±1.0V	Blank*	±0.5ppm
Blank*	3.0V±5%	1.5V±1.0	J	±1.5ppm
B	3.3V±5%	1.65V± 1.5V		
C	5.0V±5%	2.5V± 2.0V		

*3.0V±5% : Standard

Packaging	
Blank	Bulk
T	Tape and Reel

(1,000 or 2,000pcs/reel)

Table 1: Frequency Stability vs Operating Temp.

	±1ppm	±1.5ppm	±2ppm	±2.5ppm	±3ppm	±4ppm	±5ppm
0°C-50°C	D10	D15	D20	D25	D30	D40	D50
-10°C to 60°C	E10	E15	E20	E25	E30	E40	E50
0°C to 70°C		F15	F20	F25	F30	F40	F50
-20°C to +75°C			G20	G25	G30	G40	G50
-30°C to 75°C				STD	H30	H40	H50
-40°C to 85°C					I30	I40	I50

ABRACON IS
ISO 9001 / QS 9000
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale **Revised: 09.20.07**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

VOLTAGE CONTROLLED TEMPERATURE COMPENSATED CRYSTAL OSCILLATOR




5.0 X 3.2 X 1.5mm


ASVTX-09



OUTLINE DRAWING:



TAPE & REEL:



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ASVTX-09-12.800MHZ-T](#) [ASVTX-09-13.00MHZ-T](#) [ASVTX-09-14.400MHZ-T](#) [ASVTX-09-16.000MHZ-T](#) [ASVTX-09-16.800MHZ-T](#) [ASVTX-09-19.200MHZ-T](#) [ASVTX-09-19.440MHZ-T](#) [ASVTX-09-26.000MHZ-T](#) [ASVTX-09-A-24.5535MHZ-T](#) [ASVTX-09-A-19.440MHZ-T](#) [ASVTX-09-13.000MHZ-T](#) [ASVTX-09-19.800MHZ-T](#) [ASVTX-09-A-20.000MHZ-T](#) [ASVTX-09-24.5535MHZ-T](#) [ASVTX-09-A-12.800MHZ-T](#) [ASVTX-09-A-14.400MHZ-T](#) [ASVTX-09-A-16.800MHZ-T](#) [ASVTX-09-20.000MHZ-T](#) [ASVTX-09-A-19.680MHZ-T](#) [ASVTX-09-16.3676MHZ-T](#) [ASVTX-09-A-16.000MHZ-T](#) [ASVTX-09-A-13.000MHZ-T](#) [ASVTX-09-A-19.200MHZ-T](#) [ASVTX-09-A-26.000MHZ-T](#) [ASVTX-09-A-16.3676MHZ-T](#) [ASVTX-09-19.680MHZ-T](#) [ASVTX-09-A-19.800MHZ-T](#) [ASVTX-09-32.0000-I30](#)