


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	STUD SIZE	WIRE RANGE AWG	DIMENSIONS (in.)				
			A ±.03	W ±.01	C ±.01	M ±.02	H ±.02
PN22-2F	#2	#26-22	.66 (16.76)	.20 (5.08)	.19 (4.85)	.56 (14.22)	.09 (2.28)

NOTES

1. RECOMMENDED FOR:
 - A. 300V MAX. VOLTAGE RATING
 - B. #26-22 AWG SOLID OR STRANDED
COPPER WIRE
 - C. 221°F (105°C) MAX TEMP. RATING
2. MATERIAL:
 - A. STAMPING: .020 (0.51) THK COPPER,
TIN PLATED.
 - B. HOUSING: YELLOW NYLON
 - C. SLEEVE: TIN PLATED BRASS
3. PACKAGE QUANTITY: -C = 100
 -M = 1000
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS: CT-520, CT-1525
6. WIRE STRIP LENGTH : 3/16 ^{+1/32}₀ (4.76 ^{+0.8}₀)



A41234_01

										 PANDUIT CORP. TINLEY PARK, ILLINOIS			
01		JKD		ADDED CT-1525 TOOL						#26-22 BARREL NYLON INSULATED FORK			
00	7/97	TM	RLS	RELEASED	06083		LCA	RM					
REV	DATE	BY	CHK	DESCRIPTION	ECN #	QA	CUST	PM	APP	DRAWN BY TSM	CHK'D RLS	SCALE NONE	DRAWING NO. A41234

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PN22-2F-C](#) [PN22-2F-M](#)