


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



CONTACT	WIRE COLOR
1	WHITE/BLUE
2	BLUE
3	WHITE/ORANGE
4	ORANGE
5	WHITE/GREEN
6	GREEN
7	WHITE/BROWN
8	BROWN

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE PACKAGE QUANTITY.
2. 110 CONNECTORS ON BOTH ENDS. THE PATCH CORDS CAN BE USED WITH PAN-PUNCH™ 110 CONNECTING BLOCKS.
3. FEATURES INCLUDE A CLEAR CAP TO ENSURE PROPER WIRE SEQUENCE AND CONNECTOR ORIENTATION. RETAINING CLIPS SECURE THE JACKET CLOSE TO THE POINT OF TERMINATION WHICH MINIMIZES WIRE UNTWISTING. INTEGRAL STRAIN RELIEF MINIMIZES STRESS ON WIRES DURING DISCONNECTION.
4. POLARIZED TO PREVENT REVERSE INSTALLATION TO CONNECTOR BLOCK.
5. CATEGORY 5e UNSHIELDED TWISTED PAIR CABLE WITH 24AWG STRANDED TINNED COPPER CONDUCTORS.
6. DIMENSIONS IN PARENTHESES ARE IN METRIC.

PANDUIT P/N	MIN. CABLE LENGTH	WEIGHT
P110PC4IG2Y	2 FT.	.83 LB/ 10 PCS (376.5 g/ 10PCS)
P110PC4IG3Y	3 FT.	1.05 LB/ 10 PCS (476.3 g/ 10PCS)
P110PC4IG4Y	4 FT.	1.25 LB/ 10 PCS (566.9 g/ 10PCS)
P110PC4IG5Y	5 FT.	1.46 LB/ 10 PCS (662.2 g/ 10PCS)
P110PC4IG6Y	6 FT.	1.67 LB/ 10 PCS (757.5 g/ 10PCS)
P110PC4IG7Y	7 FT.	1.88 LB/ 10 PCS (852.8 g/ 10PCS)
P110PC4IG8Y	8 FT.	2.09 LB/ 10 PCS (948.0 g/ 10PCS)
P110PC4IG9Y	9 FT.	2.30 LB/ 10 PCS (1043.3g/ 10PCS)
P110PC4IG12Y	12 FT.	2.93 LB/ 10 PCS (1329.0g/ 10PCS)
P110PC4IG15Y	15 FT.	3.56 LB/ 10 PCS (1614.8g/ 10PCS)
P110PC4IG18Y	18 FT.	4.19 LB/ 10 PCS (1900.8g/ 10PCS)
P110PC4IG.5MY	.5M	.75 LB/ 10 PCS (342.0 g/ 10PCS)
P110PC4IG1MY	1M	1.09 LB/ 10 PCS (494.4 g/ 10PCS)
P110PC4IG1.5MY	1.5M	1.44 LB/ 10 PCS (653.2 g/ 10PCS)
P110PC4IG2MY	2M	1.78 LB/ 10 PCS (807.4 g/ 10PCS)
P110PC4IG3MY	3M	2.48 LB/ 10 PCS (1120.4g/ 10PCS)
P110PC4IG5MY	5M	3.85 LB/ 10 PCS (1748.1g/ 10PCS)

PART NUMBER

P110PC4IG*Y, P110PC4IG*MY

TITLE

CATEGORY 5e 110 PATCH CORD

CUSTOMER DRAWING

ITEM REVISION NAME

M02479JS/00


DATASET FILE NAME

M02479JS_DC255/00B

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]

.x ±
.xx ± .03 [.8]

.xxx ± .010 [.3]
ANGLES ±



THIRD ANGLE
PROJECTION

MATERIAL:

DRAWING NUMBER:

02479-255

PANDUIT

DRAWN BY

NER

DATE

3-17-06

CHK

WJC

SCALE

NONE

SHT 1 OF 1

SIZE

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5/28/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	02479-255
R	3-17-06	NER	WJC	RMD	RELEASED TO PRODUCTION	02479-255

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[P110PC4IG9Y](#) [P110PC4IG12Y](#) [P110PC4IG15Y](#) [P110PC4IG18Y](#)