



PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .040$	W $\pm .010$	C $\pm .020$	M $\pm .040$	H $\pm .010$
PN10-6LF-2K	#6	1.02 (25.91)	.30 (7.62)	.21 (5.33)	.79 (20.07)	.14 (3.56)
PN10-8LF-2K	#8	1.05 (26.67)	.30 (7.62)	.21 (5.33)	.79 (20.07)	.16 (4.06)
PN10-10LF-2K	#10	1.05 (26.67)	.34 (8.64)	.21 (5.33)	.79 (20.07)	.19 (4.83)

1. UL LISTED AND CSA CERTIFIED FOR :
 - A. 600 V MAX. VOLTAGE RATING
 - B. 221°F (105°C) MAX. TEMP. RATING
 - C. #12-10 AWG (2.5-6.0 mm²) SOLID OR STRANDED, COPPER WIRE
2. PACKAGE QTY. : 2K = 2000 PCS.
CONTINUOUS MOLDED CARRIER STRIP
3. MATERIAL :
 - A. STAMPING - .04" THK COPPER, TIN PLATED
 - B. HOUSING - YELLOW NYLON
 - C. SLEEVE - BRASS, TIN PLATED
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS :
 - A. PRESSES - CP-851, CP-860, CP-861
 - B. APPLICATOR - CA-800
 - C. DIE INSERTS - CD-800-3
6. WIRE STRIP LENGTH: $9/32^{+1/32}_{-0}$ (7.1^{+0.8}₋₀)



```

- .225 (5.72)
  MAX WIRE
  INSUL DIA
.130 (3.30)
MIN. WIRE
INSUL. DIA.

```

								 CORP. TINLEY PARK, ILLINOIS			
								TERMO 3PC. CONTINUOUSLY MOLDED NYLON INSULATED, 12-10 BARREL, LOCKING FORKS			
06	11/07	SRB		Removed part #PN10-14LF-2K Part Obsoleted						DRAWN BY JMV CHK'D LA SCALE NONE DRAWING NO. A41101	
REV	DATE	BY	CHK	DESCRIPTION			ECN	CUST	PM		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PN10-10LF-2K](#) [PN10-6LF-2K](#) [PN10-8LF-2K](#)