

Main

Range	Linergy
Product name	FT
Device short name	GV1G
Product or component type	Terminal block
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys - LS1 TeSys - U TeSys - K TeSys - D TeSys - GV2

Complementary

[Ie] rated operational current	63 A
Mounting location	Top
IP degree of protection	IP20 according to IEC 60529
[Ui] rated insulation voltage	690 V according to IEC 60947-1
Connections - terminals	Screw clamp terminals 1 flexible AWG 4 Screw clamp terminals 2 cable(s) 2.5...4 mm ² flexible without Screw clamp terminals 2 cable(s) 1.5...6 mm ² solid Screw clamp terminals 2 cable(s) 1.5...2 mm ² flexible with Screw clamp terminals 1 cable(s) 1.5...25 mm ² solid Screw clamp terminals 1 cable(s) 1.5...16 mm ² flexible without Screw clamp terminals 1 cable(s) 1.5...10 mm ² flexible with Screw clamp terminals 1 solid AWG 4
Tightening torque	2.2 N.m - on connector 1.7 N.m - on screw clamp terminals
Product weight	0.04 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV1G09](#)