## XCC2510PS81KGN

# absolute encoder $\varnothing$ 58 single turn - solid shaft 10 mm - push-pull 13-bit Gray

Product availability: Non-Stock - Not normally stocked in distribution facility



# Main

Commercial Status	Commercialised
Range of product	OsiSense XCC
Encoder type	Single turn absolute encoder
Encoder name	XCC
Product specific application	-
Diameter	2.28 in (58 mm)
Shaft diameter	0.39 in (10 mm)
Shaft type	Solid shaft
Resolution	8192 points
Electrical connection	1 male connector M23 radial 16 pins
Output stage	Type KG
Type of output stage	Driver push-pull gray
[Us] rated supply voltage	1130 V DC
Enclosure material	Zamak

#### Complementary

Residual ripple	0500 mV	
Maximum revolution speed	9000 rpm	
Shaft moment of inertia	0 lb.in² (10 g.cm²)	
Torque value	0.04 lbf.in (0.004 N.m)	
Maximum load	5 daN axial 10 daN radial	
Output frequency	100 kHz	
Current consumption	0100 mA no-load	
Protection type	Reverse polarity protection Short-circuit protection	
Maximum output current	20 mA	
Output level	High level: V supply - 2.5 V minimum 20 mA Low level: 0.5 V maximum 20 mA	
Surge withstand	1 kV level 2 IEC 61000-4-5	
Base material	Aluminium	
Shaft material	Stainless steel	
Type of ball bearings	6000ZZ1	
Product weight	1.03 lb(US) (0.465 kg)	

#### **Environment**

Marking	CE	
Ambient air temperature for operation	-4194 °F (-2090 °C)	
Ambient air temperature for storage	-22203 °F (-3095 °C)	
IP degree of protection	IP67 IEC 60529 IP65 IEC 60529	
Vibration resistance	10 gn (102000 Hz) IEC 60068-2-6	
Shock resistance	30 gn (11 ms) IEC 60068-2-27	
Resistance to electrostatic discharge	8 kV air discharge level 3 IEC 61000-4-2 4 kV contact discharge level 3 IEC 61000-4-2	
Resistance to electromagnetic fields	9.14 V/yd (10 V/m) level 3 IEC 61000-4-3	
Resistance to fast transients	2 kV power ports level 3 IEC 61000-4-4 1 kV signal ports level 3 IEC 61000-4-4	

### Ordering and shipping details

Category	21581 - ENCODERS, XCC	
Discount Schedule	DS2	
GTIN	003389119015486	
Nbr. of units in pkg.	1	
Package weight(Lbs)	1.02	
Product availability	Non-Stock - Not normally stocked in distribution facility	
Returnability	N	
Country of origin	FR	

## Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Compliant - since 0701 - Schneider Electric declaration of conformity

#### Contractual warranty

Period	18 months



# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric: XCC2510PS81KGN