

DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENDING VERPLICHT.


THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO JS IN CASE OF NO USAGE

03

BS, A , 201458, 002

REV.	DATE	DESCRIPTION	BY	C'K'D'
01	5-8-92	REDRAWN+CAV DIA ENLARGED	Y.D.	
02	170394	CONVERSION ME10	J.G.	
03	10/03/99	Temperature range -55C instead of -25C	K.N.	

WIRING FACE



CAT. NUMBER	A MAX.	B+0.15	C+0.2	Ø D+0.15	E+0.25	F+0.25	Ø G+0.1	Ø H+0.1	Ø J+0.1
UTG0104S	24.3	2.3	11.3	15.0	18.3	23.8	3.2	17.3	15.1
UTG0125S	24.3	2.3	11.3	19.0	20.6	26.2	3.2	21.8	18.2
UTG0128S	24.3	2.3	11.3	19.0	20.6	26.2	3.2	21.8	18.2
UTG01412S	24.3	2.3	11.3	22.2	23.0	28.6	3.2	25.0	21.4
UTG01619S	24.3	2.3	11.3	25.3	24.6	31.0	3.2	28.1	24.6
UTG01823S	24.3	2.5	11.3	28.5	26.9	33.1	3.2	31.3	27.8
UTG02028S	27.0	2.5	14.5	31.7	29.4	36.5	3.2	34.5	30.9
UTG02235S	28.0	3.5	14.5	34.9	31.6	39.3	3.2	37.7	34.1
UTG02448S	30.4	3.5	15.3	38.0	34.9	42.9	3.9	40.9	37.3
* NOTE 4									

UTG0128S AS SHOWN

## MATERIAL


- BODY : GLASS-FILLED POLYESTER UL94-V0  
COLOUR : BLACK.
- TRILOK RING : HIGH STRENGTH CuZn ALLOY,  
NICKEL PLATED.

## PERFORMANCE CHARACTERISTICS

- OPERATING TEMPERATURE : -55 °C TO +125 °C.
- INSULATION RESISTANCE : 5000 MΩ MIN.
- TEST POTENTIAL : 2000 V EFF.

## NOTES



- 1.CONNECTOR ACCEPTS ± 16 STRIP FORMED,MACHINED AND SUBMINIATURE COAXIAL PIN AND SOCKET CONTACTS.
- 2.CONTACTS TO BE ORDERED SEPARATELY : REFER TO TRIM - TRIO CATALOG.
- 3.FOR OTHER INSERT ARRANGEMENTS SEE BS,C ,201458,000
- 4.FOR WATERPROTECTED VERSION: ADD "H" TO THE CAT.NO. E.G. CAT.NO.: UTG0128SH



REAR PANEL MOUNTING

FRONT PANEL MOUNTING

GEN. ST.	01		02		03		04		05		06		07		08		0D		50		60		70		80		90				
INT. ST.	10	11	12	13	14	18	20	31	32	33	34	38	39	40	42	43	44	45	46	48	56	70	72	73	75	76	81	82	83	84	88

1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN	APPR.	DATE	SIGN.	FEMALE RECEPTACLE		
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.	DRAFT	7-6-91	M BUEDS	CAT. No. UTG---S(H)		SCALE
	CHECKED					
	PROD. MGR.			<div><div>SOURIAU Route Nationale 23 72470 CHAMPAGNE</div></div>		
	PR. ENG. MGR.					
ALL DIMENSIONS IN MM	PR. MGT. MGR.					
	REFERENCES / REFERENTIES			BS, A , 201458, 002		03
	ALLE AFMETINGEN IN MM			DRAWING NR. CUSTOMER DRAWING		REVISION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:  
UTG0103S