




Close-up of CAB.W08

CAB.W08

Specification


Part No.	CAB.W08
Product Name	CAB.W08 Taoglas Cable Assembly NMO Magnet Mount - 3/4 inch Style Brass Mount type to SMA(M) Straight Plug with 3ft (915mm) RG-58 cable

1. Cable Insertion Loss




2. RG-58 Cable Specification

2.1 Drawing - Cross Section



2.2 Structure and Dimensions



Conductor	Insulation	Braid Shield	Braid Shield	Jacket
- Material - Bare Copper Wire - Composition (1/1.02mm) - Diameter - 1.02mm	- Material - Foam Polyethylene - Avg. Thickness - 0.95mm - Diameter - 2.9 ± 0.1mm	- Material - Aluminium Foil - Construction - 0.020mm	- Material - Tinned Copper Wire - Structure - 16/6/0.12mm - Coverage - 87% - Diameter - 3.4 ± 0.05mm	- Material - RoHS PVC - Diameter - 5.0 ± 0.15mm - Colour - Black


2.3 Electrical & Physical Specification

Specification

Insulation Resistance:	1000 MΩ-Km (Min)				
Capacitance	83 ± 3 pF/m				
Nom. Impedance	53 ± 3 Ω				
Attenuation (dB/100ft)	200MHz	400MHz	700MHz	900MHz	1000MHz
	4.66	6.32	8.45	9.67	10.2



3. Technical Drawing

3.1 CAB.W08



	Name	Material	Finish	QTY
1	SMA(M) ST	Brass	Ni Plated	1
2	RG58 Coaxial Cable	PVC	Black	1
3	Heat Shrink Tube	PE	Black	1
4	NMO(MM)	Brass	Ni Plated	1

3.2 Connectors



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taoglas:](#)

[CAB.W08](#)